

T-Timing Belts

Material: Endless belts from cast polyurethane (PU), with steel tensile member.

Ordering Details: e.g.: Product No. 162 601 00, PU-Timing Belt, Profile T 5, 165 mm, Belt Width 10 mm, 33 Teeth

Metric



Profile T 5, Pitch 5 mm

Product No. Width 10mm	Product No. Width 16mm	Product No. Width 25mm	Product No. Width 32mm	Length* mm	No. of teeth
162 601 00	162 701 00	162 801 00	-	165	33
162 602 00	162 702 00	162 802 00	-	185	37
162 603 00	162 703 00	162 803 00	-	200	40
162 604 00	162 704 00	162 804 00	162 870 04	215	43
162 605 00	162 705 00	162 805 00	162 870 05	220	44
162 606 00	162 706 00	162 806 00	162 870 06	225	45
162 607 00	162 707 00	162 807 00	162 870 07	245	49
162 608 00	162 708 00	162 808 00	162 870 08	250	50
162 609 00	162 709 00	162 809 00	162 870 09	255	51
162 610 00	162 710 00	162 810 00	162 870 10	260	52
162 611 00	162 711 00	162 811 00	162 870 11	270	54
162 612 00	162 712 00	162 812 00	162 870 12	275	55
162 613 00	162 713 00	162 813 00	162 870 13	280	56
162 614 00	162 714 00	162 814 00	162 870 14	295	59
162 615 00	162 715 00	162 815 00	162 870 15	300	60
162 616 00	162 716 00	162 816 00	162 870 16	305	61
162 617 00	162 717 00	162 817 00	162 870 17	325	65
162 618 00	162 718 00	162 818 00	162 870 18	330	66
162 619 00	162 719 00	162 819 00	162 870 19	340	68
162 620 00	162 720 00	162 820 00	162 870 20	350	70
162 621 00	162 721 00	162 821 00	162 870 21	355	71
162 622 00	162 722 00	162 822 00	162 870 22	365	73
162 623 00	162 723 00	162 823 00	162 870 23	375	75
162 624 00	162 724 00	162 824 00	162 870 24	390	78
162 625 00	162 725 00	162 825 00	162 870 25	400	80
162 626 00	162 726 00	162 826 00	162 870 26	410	82
162 627 00	162 727 00	162 827 00	162 870 27	420	84
162 628 00	162 728 00	162 828 00	162 870 28	425	85
162 629 00	162 729 00	162 829 00	162 870 29	450	90
162 630 00	162 730 00	162 830 00	162 870 30	455	91
162 631 00	162 731 00	162 831 00	162 870 31	465	93
162 632 00	162 732 00	162 832 00	162 870 32	475	95
162 633 00	162 733 00	162 833 00	162 870 33	480	96
162 634 00	162 734 00	162 834 00	162 870 34	500	100
162 635 00	162 735 00	162 835 00	162 870 35	510	102
162 636 00	162 736 00	162 836 00	162 870 36	525	105
162 637 00	162 737 00	162 837 00	162 870 37	545	109
162 638 00	162 738 00	162 838 00	162 870 38	550	110
162 639 00	162 739 00	162 839 00	162 870 39	560	112
162 640 00	162 740 00	162 840 00	162 870 40	575	115
162 641 00	162 741 00	162 841 00	162 870 41	600	120
162 642 00	162 742 00	162 842 00	162 870 42	610	122
162 643 00	162 743 00	162 843 00	162 870 43	620	124
162 644 00	162 744 00	162 844 00	162 870 44	630	126
162 645 00	162 745 00	162 845 00	162 870 45	640	128
162 646 00	162 746 00	162 846 00	162 870 46	650	130
162 647 00	162 747 00	162 847 00	162 870 47	660	132
162 648 00	162 748 00	162 848 00	162 870 48	690	138
162 649 00	162 749 00	162 849 00	162 870 49	695	139
162 650 00	162 750 00	162 850 00	162 870 50	700	140
162 651 00	162 751 00	162 851 00	162 870 51	720	144
162 652 00	162 752 00	162 852 00	162 870 52	750	150
162 653 00	162 753 00	162 853 00	162 870 53	780	156
162 654 00	162 754 00	162 854 00	162 870 54	815	163
162 655 00	162 755 00	162 855 00	162 870 55	840	168
162 656 00	162 756 00	162 856 00	162 870 56	850	170
162 657 00	162 757 00	162 857 00	162 870 57	900	180
162 658 00	162 758 00	162 858 00	162 870 58	990	198
162 659 00	162 759 00	162 859 00	162 870 59	1000	200
162 660 00	162 760 00	162 860 00	162 870 60	1075	215
162 661 00	162 761 00	162 861 00	162 870 61	1100	220
162 662 00	162 762 00	162 862 00	162 870 62	1215	243
162 663 00	162 763 00	162 863 00	162 870 63	1380	276
162 664 00	162 764 00	162 864 00	162 870 64	1440	288
162 600 00	162 700 00	162 800 00	162 870 00	Open length**	

Profile T 10, Pitch 10 mm

Product No. Width 16mm	Product No. Width 25mm	Product No. Width 32mm	Product No. Width 50mm	Length* mm	No. of teeth
164 601 00	164 701 00	164 801 00	164 861 00	260	26
164 602 00	164 702 00	164 802 00	164 862 00	370	37
164 603 00	164 703 00	164 803 00	164 863 00	400	40
164 604 00	164 704 00	164 804 00	164 864 00	410	41
164 605 00	164 705 00	164 805 00	164 865 00	440	44
164 606 00	164 706 00	164 806 00	164 866 00	450	45
164 607 00	164 707 00	164 807 00	164 867 00	500	50
164 608 00	164 708 00	164 808 00	164 868 00	530	53
164 609 00	164 709 00	164 809 00	164 869 00	560	56
164 610 00	164 710 00	164 810 00	164 870 00	610	61
164 611 00	164 711 00	164 811 00	164 871 00	630	63
164 612 00	164 712 00	164 812 00	164 872 00	660	66
164 613 00	164 713 00	164 813 00	164 873 00	690	69
164 614 00	164 714 00	164 814 00	164 874 00	700	70
164 615 00	164 715 00	164 815 00	164 875 00	720	72
164 616 00	164 716 00	164 816 00	164 876 00	750	75
164 617 00	164 717 00	164 817 00	164 877 00	780	78
164 618 00	164 718 00	164 818 00	164 878 00	810	81
164 619 00	164 719 00	164 819 00	164 879 00	840	84
164 620 00	164 720 00	164 820 00	164 880 00	880	88
164 621 00	164 721 00	164 821 00	164 881 00	890	89
164 622 00	164 722 00	164 822 00	164 882 00	900	90
164 623 00	164 723 00	164 823 00	164 883 00	920	92
164 624 00	164 724 00	164 824 00	164 884 00	960	96
164 625 00	164 725 00	164 825 00	164 885 00	970	97
164 626 00	164 726 00	164 826 00	164 886 00	980	98
164 627 00	164 727 00	164 827 00	164 887 00	1010	101
164 628 00	164 728 00	164 828 00	164 888 00	1080	108
164 629 00	164 729 00	164 829 00	164 889 00	1110	111
164 630 00	164 730 00	164 830 00	164 890 00	1140	114
164 631 00	164 731 00	164 831 00	164 891 00	1150	115
164 632 00	164 732 00	164 832 00	164 892 00	1210	121
164 633 00	164 733 00	164 833 00	164 893 00	1240	124
164 634 00	164 734 00	164 834 00	164 894 00	1250	125
164 635 00	164 735 00	164 835 00	164 895 00	1300	130
164 636 00	164 736 00	164 836 00	164 896 00	1320	132
164 637 00	164 737 00	164 837 00	164 897 00	1350	135
164 638 00	164 738 00	164 838 00	164 898 00	1390	139
164 639 00	164 739 00	164 839 00	164 899 00	1400	140
164 640 00	164 740 00	164 840 00	164 900 00	1420	142
164 641 00	164 741 00	164 841 00	164 901 00	1440	144
164 642 00	164 742 00	164 842 00	164 902 00	1450	145
164 643 00	164 743 00	164 843 00	164 903 00	1460	146
164 644 00	164 744 00	164 844 00	164 904 00	1500	150
164 645 00	164 745 00	164 845 00	164 905 00	1560	156
164 646 00	164 746 00	164 846 00	164 906 00	1610	161
164 647 00	164 747 00	164 847 00	164 907 00	1750	175
164 648 00	164 748 00	164 848 00	164 908 00	1780	178
164 649 00	164 749 00	164 849 00	164 909 00	1880	188
164 650 00	164 750 00	164 850 00	164 910 00	1960	196
164 651 00	164 751 00	164 851 00	164 911 00	2250	225
164 600 00	164 700 00	164 800 00	164 860 00	Open length**	

Endless belts welded together from material sold by the meter can be supplied on request in any special length.

Belts sold by the meter and fixing plates see page 171.

Performance figures at www.maedler.de

Permissible tensile forces for the belts see page 130.



**Timing Belt Welding
within 24h-Service**

* Effective length.

** Open length from thermoplastic polyurethane (TPU), with steel tensile member.