

## Standard Timing Belt, Inch Pitch

**Material:** Neoprene with glass-fibre tensile member.  
Teeth surface fabric-coated.

Timing belt with inch dimensions, classical shape with trapezoid teeth.

Inch



Ordering Details: e.g.: Product No. 184 513 00, Standard Timing Belt, Pitch H = 1/2", Width 075, 609.6 mm

**Pitch H = 1/2" (12.7 mm)**

**Standard Width 075 (3/4" = 19.1 mm); 100 (1" = 25.4 mm); 150 (1 1/2" = 38.1 mm); 200 (2" = 50.8 mm)**

Product No. Width 075	Product No. Width 100	Product No. Width 150	Product No. Width 200	Type	Nom. Length Inch	Nom. Length mm	Number of teeth
184 513 00	184 613 00	184 713 00	184 813 00	240 H	24	609,6	48
184 515 00	184 615 00	184 715 00	184 815 00	270 H	27	685,8	54
184 517 00	184 617 00	184 717 00	184 817 00	300 H	30	762	60
184 519 00	184 619 00	184 719 00	184 819 00	330 H	33	838,2	66
184 520 00	184 620 00	184 720 00	184 820 00	360 H	36	914,4	72
184 522 00	184 622 00	184 722 00	184 822 00	390 H	39	990,6	78
184 524 00	184 624 00	184 724 00	184 824 00	420 H	42	1066,8	84
184 525 00	184 625 00	184 725 00	184 825 00	450 H	45	1143	90
184 527 00	184 627 00	184 727 00	184 827 00	480 H	48	1219,2	96
184 529 00	184 629 00	184 729 00	184 829 00	510 H	51	1295,4	102
184 531 00	184 631 00	184 731 00	184 831 00	540 H	54	1371,6	108
184 533 00	184 633 00	184 733 00	184 833 00	570 H	57	1447,8	114
184 535 00	184 635 00	184 735 00	184 835 00	600 H	60	1524	120
184 537 00	184 637 00	184 737 00	184 837 00	630 H	63	1600,2	126
184 539 00	184 639 00	184 739 00	184 839 00	660 H	66	1676,4	132
184 541 00	184 641 00	184 741 00	184 841 00	700 H	70	1778	140
184 543 00	184 643 00	184 743 00	184 843 00	750 H	75	1905	150
184 545 00	184 645 00	184 745 00	184 845 00	800 H	80	2032	160
184 547 00	184 647 00	184 747 00	184 847 00	850 H	85	2159	170
184 550 00	184 650 00	184 750 00	184 850 00	900 H	90	2286	180
184 556 00	184 656 00	184 756 00	184 856 00	1000 H	100	2540	200
184 561 00	184 661 00	184 761 00	184 861 00	1100 H	110	2794	220
184 569 00	184 669 00	184 769 00	184 869 00	1250 H	125	3175	250
184 578 00	184 678 00	184 778 00	184 878 00	1400 H	140	3556	280
184 500 00	184 600 00	184 700 00	184 800 00	H	Open length		

The pitch XH and XXH are not listed above, but can be supplied on request.

Belts sold by the meter see page 172.

Performance figures at [www.maedler.de](http://www.maedler.de)

Permissible tensile forces for the belts see page 130.