

Chain Breaker



Ordering Details: e.g.:
Product No. 140 703 00, Chain Breaker 06 B

Product No.	for DIN	Weight g
140 703 00	06 B-1, 06 B-2	910
140 705 00	081, 083, 08 B-1 and 08 B-2	915
140 707 00	10 B-1, 10 B-2, 12 B-1 and 12 B-2	1160
140 708 00	16 B-1	2020

Replacement Pin for Chain Breaker

Product No.	Matching Replacement Pin	Chain Breaker
140 713 00	140 703 00	(Type 455)
140 715 00	140 705 00	(Type 462)
140 717 00	140 707 00	(Type 501-513)
140 718 00	140 708 00	(Type 548)

Chain Puller



Ordering Details: e.g.:
Product No. 140 721 00, Chain Puller 081-12 B

Product No.	for DIN*	Weight g
140 721 00	081, 083, 08 B to 12 B	160
140 722 00	16 B to max. 65 mm	960

*can also be used for similar sizes of other standards and for double-strand and triple-strand chains.

Product No. 140 721 00 with knob.

Product No. 140 722 00 with turn lever.

Chain Lubrication Spray



Ordering Details:
Product No. 140 701 00, Chain Lubrication Spray

Product No.	Contents ml	Weight g
140 701 00	400	465

- special adhesive lubricant for the maintenance of heavy duty and fast running drives or timing chains, plain bearings, open gear units, etc.
- temperature resistant from -10° to +140°C.
- strong adhesive power.
- highly capable of creep.
- drives out water.
- dampens noise.
- protects from wear.
- protects from corrosion.
- silicone-free.



Chain Tensioners page 117



Lubricators page 854