

Pneufit Push-in šróbenia

Ø A = zodpovedajúci vonkajší priemer trubky. B = Závit (G pre valcový, R pre kuželový).
Nákresy s kompletnými rozmermi môžete nájsť na internetovej stránke www.maedler.sk

Priame prechodky s valcovým závitom

Produkt č.	Ø A mm	B
860 104 03	4	M3
860 104 05	4	M5
860 104 18	4	G ^{1/8} A
860 104 28	4	G ^{1/4} A
860 106 05	6	M5
860 106 18	6	G ^{1/8} A
860 106 28	6	G ^{1/4} A
860 108 18	8	G ^{1/8} A
860 108 28	8	G ^{1/4} A
860 108 38	8	G ^{3/8} A
860 108 48	8	G ^{1/2} A
860 110 18	10	G ^{1/8} A
860 110 28	10	G ^{1/4} A
860 110 38	10	G ^{3/8} A
860 110 48	10	G ^{1/2} A
860 112 28	12	G ^{1/4} A
860 112 38	12	G ^{3/8} A
860 112 48	12	G ^{1/2} A



Priame konektory

Produkt č.	Ø A mm
860 604 00	4
860 606 00	6
860 608 00	8
860 610 00	10
860 612 00	12



Vsúvacie tlmiče

Produkt č.	Ø A mm
861 404 00	4
861 406 00	6
861 408 00	8



Zátky

Produkt č.	Ø A mm
861 104 00	4
861 106 00	6
861 108 00	8
861 110 00	10
861 112 00	12



Redukčné / Rozširujúce sa konektory

Produkt č.	Ø A1 mm	Ø A mm
860 906 04	6	4
860 908 04	8	4
860 908 06	8	6
860 910 06	10	6
860 910 08	10	8
Rozširujúce sa		
860 904 06	4	6
860 906 08	6	8



Pneufit PUSH-IN rýchlospojky

- Teleso vyrobené najmä z poniklovanej mosadze.
- Klasický dizajn..
- Prevádzkový tlak: max. 18 bar.
- Vacuum: max. -1 bar.