

Schnellsteckverbindungen Pneufit Push-In

Ø A = passender Rohr-Außendurchmesser. B = Gewinde (G für zylindrisch, R für konisch).
Zeichnungen mit vollständiger Bemaßung im Internet unter www.maedler.de

Drehbare Winkel-Einschraubverbindungen

Artikel-Nr.	Ø A mm	B
861 704 05	4	M5
861 704 18	4	G ^{1/8} A
861 704 28	4	G ^{1/4} A
861 706 05	6	M5
861 706 18	6	G ^{1/8} A
861 706 28	6	G ^{1/4} A
861 708 18	8	G ^{1/8} A
861 708 28	8	G ^{1/4} A
861 708 38	8	G ^{3/8} A
861 710 28	10	G ^{1/4} A
861 710 38	10	G ^{3/8} A
861 710 48	10	G ^{1/2} A
861 712 28	12	G ^{1/4} A
861 712 48	12	G ^{1/2} A



T-Verbindungen

Artikel-Nr.	Ø A mm
862 604 00	4
862 606 00	6
862 608 00	8
862 610 00	10
862 612 00	12



Drehbare Winkel-Einschraubverbindungen 45°

Artikel-Nr.	Ø A mm	B mm
862 006 18	6	G ^{1/8} A
862 006 28	6	G ^{1/4} A
862 008 18	8	G ^{1/8} A
862 008 28	8	G ^{1/4} A



Kreuzverbindungen

Artikel-Nr.	Ø A mm
862 906 00	6
862 908 00	8
862 910 00	10



Winkelverbindungen

Artikel-Nr.	Ø A mm
862 104 00	4
862 106 00	6
862 108 00	8
862 110 00	10
862 112 00	12



Y-Steckverbindungen

Artikel-Nr.	Ø A mm	Ø A1 mm
863 004 00	1x4	2x4
863 006 00	1x6	2x6
863 008 00	1x8	2x8
863 010 00	1x10	2x10
863 006 04	1x6	2x4
863 008 06	1x8	2x6
863 010 08	1x10	2x8



Drehbare Winkel-Schottverbindungen

Artikel-Nr.	Ø A mm
862 206 00	6
862 208 00	8
862 210 00	10



Winkel-Steckverbindungen

Artikel-Nr.	Ø A mm	Ø A1 mm
862 304 00	4	4
862 306 00	6	6
862 308 00	8	8



Pneufit Push-In Schnellsteckverbindungen

- Gehäuse überwiegend aus Messing vernickelt.
- Klassische Ausführung.
- Betriebsdruck: max. 18 bar
- Vakuum: max. -1 bar.