


Uhlový otočný spoj s tesniacim krúžkom

Material: Mosadz, poniklovaná.



Informácie potrebné na objednanie: napr.: Produkt č. 863 504 05, Uhlový otočný spoj s tesniacim krúžkom, Vonkajšia trubka-Ø 4 mm, Závit M5

Produkt č.	Ø A mm	B	D mm	D1 mm	SW mm	Ø F mm	G mm	Hmot. g
863 504 05	4	M5	18,7	22	8	9,5	4,0	13
863 504 18	4	G ^{1/8} A	20,6	30	14	11,0	6,0	34
863 506 05	6	M5	22,2	22	8	12,5	4,0	17
863 506 28	6	G ^{1/4} A	24,2	34	17	13,0	7,4	54
863 508 18	8	G ^{1/8} A	23,7	30	14	14,0	6,0	37
863 508 28	8	G ^{1/4} A	24,7	34	17	14,0	7,4	56
863 508 38	8	G ^{3/8} A	26,7	41	22	16,5	9,0	112
863 510 28	10	G ^{1/4} A	30,2	34	17	16,0	7,4	59


Uhlový otočný spoj s regulačným ventilom a tesniacim krúžkom

Material: Mosadz, poniklovaná.

Symbol



Informácie potrebné na objednanie: napr.: Produkt č. 863 604 05, Uhlový otočný spoj a regulačný ventil, s tesniacim krúžkom, Vonkajšia trubka-Ø 4 mm, Závit M5




Produkt č.	Ø A mm	B	D mm	D1 mm	SW mm	Ø F mm	G mm	Hmot. g
863 604 05	4	M5	18,7	27,0	8	9,5	4,4	13
863 604 18	4	G ^{1/8} A	20,6	34,0	14	11,0	6,0	34
863 606 05	6	M5	22,2	27,0	8	12,5	4,4	17
863 606 18	6	G ^{1/8} A	23,7	34,0	14	12,5	6,0	37
863 606 28	6	G ^{1/4} A	24,2	36,5	17	13,0	6,0	58
863 608 28	8	G ^{1/4} A	24,7	36,5	17	14,0	6,0	59
863 608 38	8	G ^{3/8} A	26,7	51,5	22	16,5	10,0	123
863 608 18	8	G ^{1/8} A	23,7	34,0	14	13,5	6,0	39
863 610 28	10	G ^{1/4} A	30,2	36,5	17	15,7	6,0	63

Otočné skrutky s tesniacimi krúžkami

Materialy: Mosadz, poniklovaná.

Pre kombinácie s uhlovými otočnými spojmi.



Informácie potrebné na objednanie: napr.: Produkt č. 864 700 18, Otočná skrutka s tesniacimi krúžkami, G^{1/8}A

Produkt č.	B	D1 mm	SW mm	Ø S mm	Hmot. g
864 700 18	G ^{1/8} A	30	14	5,0	15
864 700 28	G ^{1/4} A	31,5	17	8,5	25
864 700 38	G ^{3/8} A	41	22	10,0	60