

BALLISTOL® Maintenance and Repair Sprays

BALLISTOL® 21150 Universal Oil, liquid



Ordering details: e.g.: Product No. 140 701 61, BALLISTOL Universal Oil, liquid

Product No.	Contents in ml	Weight in g
140 701 61	500	580

BALLISTOL Universal Oil cleans, maintains, protects, preserves, dissolves unwanted residues and provides rust protection without gumming up.

- extremely creepable.
- sliding active.
- completely biodegradable.
- food safe.
- skin-compatible.
- completely harmless according to §§ 30,31 LFGB and EG Regulation No. 1935/2004.

BALLISTOL® 21810 Universal Oil, Spray



Ordering details: e.g.: Product No. 140 701 62, BALLISTOL Universal Oil, Spray

Product No.	Contents in ml	Weight in g
140 701 62	400	450

BALLISTOL Universal Oil Spray cleans, maintains, protects, preserves, dissolves unwanted residues and provides rust protection without gumming up.

- extremely creepable.
- sliding active.
- completely biodegradable.
- food safe.
- skin-compatible.
- completely harmless according to §§ 30,31 LFGB and EG Regulation No. 1935/2004.
- Danger (5) H222, H229

BALLISTOL® 21727 Universal Oil, VarioFlex



Ordering details: e.g.: Product No. 140 701 63, BALLISTOL Universal Oil, VarioFlex-Spray

Product No.	Contents in ml	Weight in g
140 701 63	350	370

BALLISTOL Universal Oil Spray cleans, maintains and protects. The capillary tube with memory effect can be bent individually.

- extremely creepable.
- sliding active.
- completely biodegradable.
- food safe.
- skin-compatible.
- completely harmless according to §§ 30,31 LFGB and EG Regulation No. 1935/2004.
- Danger (5) H225, H412.

BALLISTOL® 25200 Copper-Graphite-Spray



Ordering details: e.g.: Product No. 140 701 64, BALLISTOL Copper-Graphite-Spray

Product No.	Contents in ml	Weight in g
140 701 64	200	230

BALLISTOL Copper-Graphite-Spray facilitates assembly and prevents seizing and jamming of components.

- silicone-, PTFE-, acid- and resin-free.
- reliably prevents seizing.
- reduces friction losses.
- ideal for threads and fits.
- prevents contact corrosion at different metals.
- temperature range: -50°C to +1,000°C.
- Danger (5) H222, H229, H412.

BALLISTOL® 25261 Premium Rust Protection Oil



Ordering details: e.g.: Product No. 140 701 65, BALLISTOL Premium Rust Protection Oil

Product No.	Contents in ml	Weight in g
140 701 65	400	420

BALLISTOL Premium Rust Protection Oil Spray is used for the care, maintenance and protection of machines, equipment, precision tools, measuring instruments, moulds and stamping presses.

- silicone-, PTFE-, acid- and resin-free.
- ideal for long-term preservation in high atmospheric humidity and aggressive ambient air.
- protects against rust for a long time.
- displaces moisture.
- temperature range: -40°C to +150°C.
- Danger (5) H222, H229, H412.

BALLISTOL® 25307 Silicone-Oil



Ordering details: e.g.: Product No. 140 701 66, BALLISTOL Silicone-Oil

Product No.	Contents in ml	Weight in g
140 701 66	400	450

BALLISTOL Silicone-Oil-Spray for the lubrication and protection of parts made of rubber, plastic and metal.

Typical applications: Plastic gears, plastic bearings, rubber bearings, cable pulls, guide rails, guides, rollers, slideways.

- PTFE-, acid- and resin-free.
- very economical with a high silicone content.
- lubrication free of mineral oil.
- Danger (1, 2, 5) H222, H229, H315, H336, H411.

BALLISTOL® 25607 Teflon™-Spray



Ordering details: e.g.: Product No. 140 701 67, BALLISTOL Teflon™-Spray

Product No.	Contents in ml	Weight in g
140 701 67	400	450

BALLISTOL Teflon™-Spray on PTFE-basis for a consistent and durable lubrication and sliding activity without oil or grease content.

- silicone-, acid- and resin-free.
- clean dry lubrication without adhering dirt and oily hands.
- effective reduction of static, sliding and rolling friction.
- no annoying lubricant sludge.
- hygienic, clean and nature-friendly.
- Danger (1, 5) H222, H229, H319.

BALLISTOL® 22960 Garage-Oil



Ordering details: e.g.: Product No. 140 701 68, BALLISTOL Garage-Oil

Product No.	Contents in ml	Weight in g
140 701 68	400	440

BALLISTOL Garage-Oil-Spray is ideal for the maintenance and care of machines and equipment of all kinds.

- silicone-, PTFE-, acid- and resin-free.
- effortlessly removes flash rust and cleans from foreign particles.
- keeps moving parts running smoothly.
- protects iron, steel and non-ferrous metals from rust and corrosion.
- tested according to DIN 50 021-SS (salt chamber spray test).
- Danger (5) H222, H229, H412.

H222 Extremely flammable aerosol.
 H225 Highly flammable liquid and vapour.
 H229 Pressurised container: May burst if heated.
 H315 Causes skin irritation.
 H319 Causes serious eye irritation.
 H336 May cause drowsiness or dizziness.
 H411 Toxic to aquatic life with long lasting effects.
 H412 Harmful to aquatic life with long lasting effects.



Safety Data Sheets at www.maedler.de in the section Downloads

BALLISTOL® Maintenance and Repair Sprays

BALLISTOL® 25350 Multi-Purpose Grease



Ordering details: e.g.: Product No. 140 701 69,
BALLISTOL Multi-Purpose Grease

Product No.	Contents in g	Weight in g
140 701 69	400	500

BALLISTOL Multi-Purpose Grease for use in the lubrication of sliding and roller bearings.

- silicone-, PTFE-, acid- and resin-free.
- very good water resistance.
- reliable long-term lubrication.
- good sealing behaviour.
- recommended for central lubrication systems.
- complies with DIN 51825: KP 2 K-30 & ISO 6743-9: ISO-L-XCCHB 2.
- temperature range: -35°C to +130°C.

BALLISTOL® 25075 Universal- & Plastic Cleaner



Ordering details: e.g.: Product No. 140 701 70,
BALLISTOL Universal- & Plastic Cleaner

Product No.	Contents in ml	Weight in g
140 701 70	750	830

BALLISTOL Universal & Plastic Cleaner for powerful cleaning.

- high dirt dissolving power for grease and oil.
- no wiping with water necessary.
- removes 99.9% of bacteria.
- short reaction time.
- has an antistatic effect.
- dust and dirt repellent.
- gentle on materials.
- silicone-free, solvent-free.

BALLISTOL®-Set Engineering Box



Ordering details: e.g.: Product No. 140 701 75,
BALLISTOL-Set Engineering Box

Product No.	Contents in ml	Weight in g
140 701 75	1,200	2,24

BALLISTOL Engineering Set contains everything you need in a well-stocked workshop.

- 200 ml Teflon™-Spray for dry lubrication.
- 200 ml Copper-Graphite-Spray as a silicone-free lubricant and corrosion protection.
- 200 ml Silicone-Oil Spray for lubrication.
- 200 ml Premium Rust Protection Oil-Spray.
- 200 ml Garage-Oil.
- 200 ml Ballistol Universal Oil.
- 1 x cotton cloth.
- Danger (1, 2 ,5) H222, H229, H315, H319, H336, H411, H412.

H222 Extremely flammable aerosol.
H229 Pressurised container: May burst if heated.
H315 Causes skin irritation.
H319 Causes serious eye irritation.
H336 May cause drowsiness or dizziness.
H411 Toxic to aquatic life with long lasting effects.
H412 Harmful to aquatic life with long lasting effects.



Safety Data Sheets at www.maedler.de in the section Downloads