




- GB** Slide installation
- D** Schienenbefestigung
- F** Montage de la glissière
- I** Montaggio guida
- E** Instalación de la guía

**i**

Einbau-Breite X  
= Schienenbreite  
+0,2 / +0,5 mm

Largeur de montage X  
= largeur de glissière  
+0,2/+0,5 mm

Mounting Width X  
= Slide Width +0,2 / +0,5 mm



**GB** All fixings positions must be used to achieve maximum load rating.

**D** Es sind alle Befestigungspositionen zu verwenden, damit der maximale Lastwert erzielt wird.

**F** Tous les points de fixation doivent être utilisés pour obtenir la charge maximale.

**I** Per ottenere il massimo carico nominale, devono essere usate tutte le posizioni di fissaggio.

**E** Todas las posiciones de fijación deben ser usadas para se conseguir la capacidad máxima de carga.



GB All fixings positions must be used to achieve maximum load rating.

D Es sind alle Befestigungspositionen zu verwenden, damit der maximale Lastwert erzielt wird.

F Tous les points de fixation doivent être utilisés pour obtenir la charge maximale.

I Per ottenere il massimo carico nominale, devono essere usate tutte le posizioni di fissaggio.

E Todas las posiciones de fijación deben ser usadas para se conseguir la capacidad máxima de carga.