


**Typ TR67-40**

Force stroke statically

$E_{ges}$ : 17,5 Nm,  $E_{abs}$ : 2,7 Nm, efficiency factor: 15%



**Typ TR67-40**

Kraft- Wegkennlinie, dynamisch

$E_{ges}$ : 23,0 Nm,  $E_{abs}$ : 6,2 Nm, Wirkungsgrad: 27%

