

## Maintenance and Repair Sprays WD-40®

### WD-40® Multi-Use Product Smart Straw®



Ordering Details: e.g.: Product No. 140 701 15,  
WD-40 Multi-Use Product Smart Straw, 400 ml

Product No.	Contents in ml	Weight in g
140 701 15	400	437

Multipurpose oil spray with multiple application possibilities. Spray head can be repositioned for area or spot spraying.

- Rust remover.
- penetrating oil.
- lubricant.
- displacement of moisture.
- corrosion protection.
- cleaner.
- silicone-free.
- Danger (1, 5) H222, H229, H304, H336

### WD-40 Flexible® Multi-Use Product



Ordering Details: e.g.: Product No. 140 701 18,  
WD-40 Flexible, 400 ml

Product No.	Contents in ml	Weight in g
140 701 18	400	580

Multipurpose oil spray with multiple application possibilities. Spray tube made of metal, which can be bent individually.

- Rust remover.
- penetrating oil.
- lubricant.
- displacement of moisture.
- corrosion protection.
- cleaner.
- silicone-free.
- Danger (1, 5) H222, H229, H304, H336

### WD-40® Multi-Use Product Classic



Ordering Details: e.g.: Product No. 140 701 20,  
WD-40 Multi-Use Product Classic, 100 ml

Product No.	Contents in ml	Weight in g
140 701 20	100	131
140 701 21	400	437

Multipurpose oil spray with multiple application possibilities.

- Rust remover.
- penetrating oil.
- lubricant.
- displacement of moisture.
- corrosion protection.
- cleaner.
- silicone-free.
- Danger (1, 5) H222, H229, H304, H336

### WD-40® Multi-Use Product 5 L Container



Ordering Details: e.g.: Product No. 140 701 22,  
WD-40 Multi-Use Product 5 L Container

Product No.	Contents in l	Weight in kg
140 701 22	5	4,27

Multipurpose oil with multiple application possibilities in a 5 litre plastic canister.

- Rust remover.
- penetrating oil.
- lubricant.
- displacement of moisture.
- corrosion protection.
- cleaner.
- silicone-free.
- Danger (1, 2, 4) H226, H304, H336

### WD-40® Multi-Use Product 5 L incl. Spray Applicator



Ordering Details: e.g.: Product No. 140 701 24,  
WD-40 Multi-Use Product 5 L incl. Spray Applicator

Product No.	Contents in l	Weight in kg
140 701 24	5	4,5

Multi-purpose oil with multiple application possibilities in a 5 litre plastic canister, with an empty hand sprayer.

- Rust remover.
- penetrating oil.
- lubricant.
- displacement of moisture.
- corrosion protection.
- cleaner.
- silicone-free.
- Danger (1, 2, 4) H226, H304, H336

### WD-40® Multi-Use Product Spray Applicator, empty



Ordering Details: e.g.: Product No. 140 701 30,  
WD-40 Multi-Use Product Spray Applicator, empty

Product No.	Contents in l	Weight in g
140 701 30	up to 600	91

The WD-40 Hand sprayer is designed for use with WD-40 Multi-Use products from canisters. With an adjustable spray nozzle, it is ideal to spray over a large area. Its ergonomic spray head and long handle and 600ml capacity make it easy to use. The spray applicator is sold empty.

### WD-40 Specialist® Penetrant



Ordering Details: e.g.: Product No. 140 701 40,  
WD-40 Specialist Penetrant, 100 ml

Product No.	Contents in ml	Weight in g
140 701 40	100	115
140 701 41	400	414

The special spray quickly separates rusted and corroded parts. Spray head (only 400 ml) can be adjusted for area or spot spraying.

- quickly penetrates rusted and corroded parts.
- highly water resistant.
- very low surface tension to penetrate rust.
- Temperature range: -20°C to +90°C
- Danger (1, 2, 5) H222, H229, H304, H315, H336, H411

### WD-40 Specialist® PTFE Lubricant



Ordering Details: e.g.: Product No. 140 701 42,  
WD-40 Specialist PTFE Lubricant, 400 ml

Product No.	Contents in ml	Weight in g
140 701 42	400	374

The special spray extends the life expectancy of tools and equipment. Spray head can be adjusted for area or spot spraying

- reduces friction and wear.
- for use on metal, glass, vinyl, rubber and plastic.
- Long-lasting formula with excellent lubricating properties.
- Temperature range: -20°C to +100°C.
- Danger (1, 2, 5) H222, H229, H304, H315, H336, H411

H222 Extremely flammable aerosol.  
H229 Pressurised container: May burst if heated.  
H304 May be fatal if swallowed and enters airways.  
H315 Causes skin irritation.  
H336 May cause drowsiness or dizziness.  
H411 Toxic to aquatic life with long lasting effects.



Safety Data Sheets at [www.maedler.de](http://www.maedler.de) in the section Downloads

## Maintenance and Repair Sprays WD-40®

### WD-40 Specialist® Dry PTFE Lubricant



Ordering Details: e.g.: Product No. 140 701 43,  
WD-40 Specialist Dry PTFE Lubricant, 400 ml

Product No.	Contents in ml	Weight in g
140 701 43	400	387

Special spray, for improved lubricating and protective properties. Dual action Smart Straw® applicator for wide area and precision spray applications.

- reduces friction and wear.
- ideal to be used on metals, plastic and glass.
- leaves a clear, dry film.
- advanced formulation works as an effective mould release agent.
- Temperature range: -45°C to +260°C.
- Danger (1, 2, 5) H222, H229, H304, H315, H336, H411

### WD-40 Specialist® White Lithium Grease



Ordering Details: e.g.: Product No. 140 701 44,  
WD-40 Specialist White Lithium Grease, 400 ml

Product No.	Contents in ml	Weight in g
140 701 44	400	363

Special spray for long-lasting lubrication without dripping or running off. Spray head can be adjusted for area or spot spraying

- for use on metal to metal connections.
- Water and heat resistant lubricant.
- ideal for load bearing application.
- Temperature range: -25°C to +130°C.
- Danger (1, 2, 5) H222, H229, H304, H315, H336, H411

### WD-40 Specialist® Silicone Lubricant



Ordering Details: e.g.: Product No. 140 701 45,  
WD-40 Specialist Silicone Lubricant, 100 ml

Product No.	Contents in ml	Weight in g
140 701 45	100	115
140 701 46	400	374

The special spray with excellent lubricating properties is water-repellent and protects against moisture. Spray head (only 400 ml) can be adjusted for area or spot spraying.

- Formulated for improved high pressure performance.
- Prevents rust and corrosion.
- avoids jamming and blockages.
- colourless.
- Temperature range: -35°C to +200°C.
- Danger (1, 5) H222, H229, H304, H336

### WD-40 Specialist® Cutting Oil



Ordering Details: e.g.: Product No. 140 701 47,  
WD-40 Specialist Cutting Oil, 400 ml

Product No.	Contents in ml	Weight in g
140 701 47	400	473

The special spray improves machining processes for all metals. Spray head can be adjusted for area or spot spraying.

- Contains Extreme Pressure and Anti Wear additives.
- Extends tool life.
- Danger (2, 5) H222, H229, H362, H400, H410

### WD-40 Specialist® Contact Cleaner



Ordering Details: e.g.: Product No. 140 701 50,  
WD-40 Specialist Contact Cleaner, 100 ml

Product No.	Contents in ml	Weight in g
140 701 50	100	115
140 701 51	400	348

Special Spray that cleans oil, dirt, flux residue and condensation from sensitive electronics and electrical equipment. Spray head (only 400 ml) can be adjusted for area or spot spraying.

- fast active non conductive cleaner.
- penetrates quickly and leaves no residue.
- penetrates in those hard to reach areas.
- Danger (1, 2, 5) H222, H229, H304, H315, H319, H336, H411

### WD-40 Specialist® Lock Lube



Ordering Details: e.g.: Product No. 140 701 52,  
WD-40 Specialist Lock Lube, 100 ml

Product No.	Contents in ml	Weight in g
140 701 52	100	126

The special spray has been specially developed for the maintenance of all types of locking cylinders.

- penetrates and dissolves.
- lubricates and protects.
- prevents wear.
- Temperature range: -70°C to +150°C.
- Danger (1, 5) H222, H229, H304, H336

### WD-40 Specialist® Brake Cleaner



Ordering Details: e.g.: Product No. 140 701 54,  
WD-40 Specialist Brake Cleaner, 500 ml

Product No.	Contents in ml	Weight in g
140 701 54	500	470

The special spray effectively removes grease, oil, dirt and deposits from brakes, clutch, gearbox and other components.

- residue-free.
- works immediately:
- powerful spray.
- extremely flammable.
- for use at room temperature.
- Danger (1, 2, 5) H222, H229, H315, H319, H336, H411

### WD-40 Specialist® Degreaser



Ordering Details: e.g.: Product No. 140 701 55,  
WD-40 Specialist Degreaser, 500 ml

Product No.	Contents in ml	Weight in g
140 701 55	500	500

The special spray removes grease, oil, dirt and soot. This product is particularly suitable for metals. Spray head can be adjusted for area or spot spraying.

- cleans equipment to make it run smoother and last longer.
- works immediately on contact.
- easy to rinse and leaves no residue.
- can be used on a variety of surfaces, including metal.
- extremely flammable.
- Danger (1, 5) H222, H229, H304, H336

H222 Extremely flammable aerosol.  
H229 Pressurised container: May burst if heated.  
H304 May be fatal if swallowed and enters airways.  
H315 Causes skin irritation.  
H319 Causes serious eye irritation.  
H336 May cause drowsiness or dizziness.  
H362 May cause harm to breast-fed children.  
H400 Very toxic to aquatic life.  
H410 Very toxic to aquatic life with long lasting effects.  
H411 Toxic to aquatic life with long lasting effects.



Safety Data Sheets at [www.maedler.de](http://www.maedler.de) in the section Downloads