


Stirnverzahnte Wellen aus Stahl mit einseitigem Nabenansatz, gefräste Zähne, gerade verzahnt

Werkstoff:

11SMnPb30 bis 80 mm Ø, darüber C45.
Eingriffswinkel 20°.



Bestellangaben: z.B.: Art.-Nr. 214 511 00, Stirnzahnwelle, Modul 1, 11 Zähne

Modul 1,0

| Artikel-Nr. | Zähnezahl | d mm | d _a mm | ND mm | NL mm | b mm | L mm | Gewicht kg |
|-------------|-----------|------|-------------------|-------|-------|------|------|------------|
| 214 511 00 | 11 | 11 | 13 | 12 | 50 | 150 | 200 | 0,14 |
| 214 513 00 | 13 | 13 | 15 | 12 | 50 | 150 | 200 | 0,18 |
| 214 514 00 | 14 | 14 | 16 | 12 | 50 | 150 | 200 | 0,21 |
| 214 516 00 | 16 | 16 | 18 | 12 | 50 | 150 | 200 | 0,27 |
| 214 517 00 | 17 | 17 | 19 | 16 | 50 | 150 | 200 | 0,33 |
| 214 519 00 | 19 | 19 | 21 | 16 | 50 | 180 | 230 | 0,46 |
| 214 521 00 | 21 | 21 | 23 | 16 | 50 | 180 | 230 | 0,55 |
| 214 523 00 | 23 | 23 | 25 | 16 | 50 | 180 | 230 | 0,64 |
| 214 527 00 | 27 | 27 | 29 | 16 | 50 | 180 | 230 | 0,86 |
| 214 531 00 | 31 | 31 | 33 | 16 | 50 | 180 | 230 | 1,12 |
| 214 535 00 | 35 | 35 | 37 | 16 | 50 | 180 | 230 | 1,40 |
| 214 537 00 | 37 | 37 | 39 | 16 | 50 | 180 | 230 | 1,56 |
| 214 545 00 | 45 | 45 | 47 | 16 | 50 | 180 | 230 | 2,28 |
| 214 552 00 | 52 | 52 | 54 | 16 | 50 | 180 | 230 | 3,02 |
| 214 557 00 | 57 | 57 | 59 | 16 | 50 | 180 | 230 | 3,61 |

Modul 1,5

| Artikel-Nr. | Zähnezahl | d mm | d _a mm | ND mm | NL mm | b mm | L mm | Gewicht kg |
|-------------|-----------|------|-------------------|-------|-------|------|------|------------|
| 218 513 00 | 13 | 19,5 | 22,5 | 16 | 50 | 150 | 200 | 0,41 |
| 218 514 00 | 14 | 21 | 24 | 16 | 50 | 150 | 200 | 0,46 |
| 218 516 00 | 16 | 24 | 27 | 16 | 50 | 150 | 200 | 0,58 |
| 218 517 00 | 17 | 25,5 | 28,5 | 16 | 50 | 180 | 230 | 0,77 |
| 218 519 00 | 19 | 28,5 | 31,5 | 16 | 50 | 180 | 230 | 0,94 |
| 218 521 00 | 21 | 31,5 | 34,5 | 16 | 50 | 180 | 230 | 1,14 |
| 218 527 00 | 27 | 40,5 | 43,5 | 16 | 50 | 180 | 230 | 1,84 |
| 218 532 00 | 32 | 48 | 51 | 16 | 50 | 180 | 230 | 2,57 |
| 218 542 00 | 42 | 63 | 66 | 16 | 30 | 220 | 250 | 5,31 |

Modul 2,0

| Artikel-Nr. | Zähnezahl | d mm | d _a mm | ND mm | NL mm | b mm | L mm | Gewicht kg |
|-------------|-----------|------|-------------------|-------|-------|------|------|------------|
| 241 513 00 | 13 | 26 | 30 | 16 | 50 | 200 | 250 | 0,87 |
| 241 514 00 | 14 | 28 | 32 | 16 | 50 | 200 | 250 | 0,99 |
| 241 516 00 | 16 | 32 | 36 | 16 | 50 | 200 | 250 | 1,28 |
| 241 517 00 | 17 | 34 | 38 | 16 | 50 | 200 | 250 | 1,44 |
| 241 519 00 | 19 | 38 | 42 | 16 | 50 | 200 | 250 | 1,79 |
| 241 521 00 | 21 | 42 | 46 | 16 | 50 | 200 | 250 | 2,17 |
| 241 523 00 | 23 | 46 | 50 | 16 | 50 | 200 | 250 | 2,61 |
| 241 527 00 | 27 | 54 | 58 | 16 | 30 | 220 | 250 | 3,89 |
| 241 529 00 | 29 | 58 | 62 | 16 | 30 | 220 | 250 | 4,49 |
| 241 542 00* | 42 | 84 | 88 | 16 | 30 | 220 | 250 | 9,48 |

* Material C45