


Slides 2026, Width 9.5 mm, to 49 kg, Two-Way Travel

Material:


Slide elements: Cold-rolled steel, zinc plated.
 Ball retainers: Cold-rolled, zinc-plated steel.
 Balls: Hardened steel.

Telescopic ball bearing slides for applications in the industrial and electronics sector.

- Hold-out on both sides.
- Pulls out to front and back. For applications requiring access from both sides of the drawer.
- Service life 10,000 cycles.



Ordering details: e.g.: Prod. No. 649 004 30, Slides 2026



Product No. per Pair	Slide Length mm	Travel +/-3.2 mm	A mm	B mm	C mm	D mm	Load Rating per Pair kg	Weight per Pair kg
649 004 30	300	211.3	128	160	224	256	49	0.6
649 004 35	350	248.6	160	192	256	288	47	0.7
649 004 40	400	285.9	192	224	320	352	43	0.7
649 004 45	450	323.2	224	256	352	384	41	0.8
649 004 50	500	360.5	256	288	416	448	37	0.9
649 004 55	550	397.8	256	288	480	512	34	1.0
649 004 60	600	435.1	288	320	512	544	30	1.1
649 004 65	650	472.4	288	320	576	608	27	1.2
649 004 70	700	509.7	320	352	608	640	25	1.3

Note

Recommended mounts: M4 screw.
 Use all mounting positions to achieve the max. load rating.