

Slides 2642, Width 12.7 mm, to 34 kg, Compact Profile, Full Extension


Material:

Slide elements: Cold-rolled steel, zinc plated.
Ball retainers: Cold-rolled, zinc-plated steel.
Balls: Hardened steel.


Telescopic ball bearing slides for applications in the industrial and electronics sector.

- Low slide profile.
- Groove or side mounting option.
- Hold-in in closed position.
- Service life 10,000 cycles.

Ordering details: e.g.: Prod. No. 649 008 20, Slides 2642



Accuride



Product No. per Pair	Slide Length mm	Travel +/-3.2 mm	A mm	B mm	C mm	D mm	E mm	Load Rating per Pair kg	Weight per Pair kg
649 008 20	200	209	128	-	-	-	-	16	0.46
649 008 25	250	259	128	-	-	-	-	23	0.59
649 008 30	300	308	128	224	-	-	-	32	0.69
649 008 35	350	357	128	224	-	-	-	34	0.80
649 008 40	400	406	128	224	320	-	-	32	0.93
649 008 45	450	456	128	224	352	-	-	29	1.06
649 008 50	500	505	128	224	352	416	-	29	1.18
649 008 55	550	554	128	224	352	448	489	27	1.29

Note

Recommended mount: M4/M6 screw.
Head-Ø max. 7.8 mm, Head length max. 2 mm.
Use all mounting positions to achieve the max. load rating.