


## Manifold

**Material:** Body made from plastic.  
With Push-In connections.




Ordering details: e.g.: Product No. 863 308 04, Manifold, Tube outer Ø Inlet 8 mm, Tube Outer-Ø Outlet 4 mm

Product No.	Ø A mm	Ø A1 mm	C mm	D mm	E mm	H mm	J mm	K mm	L mm	M mm	N mm	P mm	Weight g
863 308 04	8	4	68	42	13	3.4	12.7	16	14	9.0	20.0	16.4	38
863 308 06	8	6	68	42	13	3.4	12.7	16	14	9.0	20.2	16.4	42
863 310 08	10	8	83	48	15	3.4	17.2	20	16	10.5	22.7	20.4	67

## Elbow Banjo Assembly with Sealing Ring

**Material:** Brass, nickel plated.




Ordering details: e.g.: Product No. 863 504 05, Elbow Banjo Assembly with Sealing Ring, Tube Outer-Ø 4 mm, Thread M5

Product No.	Ø A mm	B	D mm	D1 mm	SW mm	Ø F mm	G mm	Weight g
863 504 05	4	M5	18.7	22	8	9.5	4.0	13
863 504 18	4	G <sup>1</sup> / <sub>8</sub> A	20.6	30	14	11.0	6.0	34
863 506 05	6	M5	22.2	22	8	12.5	4.0	17
863 506 28	6	G <sup>1</sup> / <sub>4</sub> A	24.2	34	17	13.0	7.4	54
863 508 18	8	G <sup>1</sup> / <sub>8</sub> A	23.7	30	14	14.0	6.0	37
863 508 28	8	G <sup>1</sup> / <sub>4</sub> A	24.7	34	17	14.0	7.4	56
863 508 38	8	G <sup>3</sup> / <sub>8</sub> A	26.7	41	22	16.5	9.0	112
863 510 28	10	G <sup>1</sup> / <sub>4</sub> A	30.2	34	17	16.0	7.4	59

## Elbow Banjo Assembly, Regulating Out, with Sealing Ring

**Material:** Brass, nickel plated.



Ordering details: e.g.: Product No. 863 604 05, Elbow Banjo Assembly, Regulating Out, with Sealing Ring, Tube Outer-Ø 4 mm, Thread M5

Symbol	Product No.	Ø A mm	B	D mm	D1 mm	SW mm	Ø F mm	G mm	Weight g
	863 604 05	4	M5	18.7	27.0	8	9.5	4.4	13
	863 604 18	4	G <sup>1</sup> / <sub>8</sub> A	20.6	34.0	14	11.0	6.0	34
	863 606 05	6	M5	22.2	27.0	8	12.5	4.4	17
	863 606 18	6	G <sup>1</sup> / <sub>8</sub> A	23.7	34.0	14	12.5	6.0	37
	863 606 28	6	G <sup>1</sup> / <sub>4</sub> A	24.2	36.5	17	13.0	6.0	58
	863 608 28	8	G <sup>1</sup> / <sub>4</sub> A	24.7	36.5	17	14.0	6.0	59
	863 608 38	8	G <sup>3</sup> / <sub>8</sub> A	26.7	51.5	22	16.5	10.0	123
	863 608 18	8	G <sup>1</sup> / <sub>8</sub> A	23.7	34.0	14	13.5	6.0	39
	863 610 28	10	G <sup>1</sup> / <sub>4</sub> A	30.2	36.5	17	15.7	6.0	63