


Standard Pulleys, Inch Pitch ISO 5294



Material: Up to a Teeth Number of 48 phosphated steel, from a Teeth Number of 50 grey cast iron GG25. Pre-bored.


Ordering Details: e.g.: Product No. 182 110 00, Pulleys, Pitch L = 3/8", 10 Teeth, Timing Belt Width 050, 2 Flanges

L 050: Pitch 3/8" = 9.525 mm for Timing Belt Width 0.50" = 12.7 mm

Product No.	Number of teeth	Type	De mm	Df mm	d mm	ND mm	b mm	L mm	B mm	Weight kg
182 110 00	10	1F	29,56	36	30,33	20	19	28	8	0,11
182 111 00	11	1F	32,59	36	33,35	24	19	30	8	0,13
182 112 00	12	1F	35,62	42	36,38	24	19	30	8	0,17
182 113 00	13	1F	38,65	44	39,41	28	19	30	8	0,20
182 114 00	14	1F	41,68	48	42,45	28	19	30	8	0,23
182 115 00	15	1F	44,72	51	45,48	34	19	30	8	0,29
182 116 00	16	1F	47,75	54	48,51	36	19	32	8	0,34
182 117 00	17	1F	50,78	57	51,54	36	19	32	10	0,37
182 118 00	18	1F	53,81	60	54,57	40	19	32	10	0,43
182 119 00	19	1F	56,84	63	57,61	40	19	32	10	0,47
182 120 00	20	1F	59,88	66	60,64	40	19	32	10	0,51
182 121 00	21	1F	62,91	71	63,67	45	19	32	10	0,58
182 122 00	22	1F	65,94	75	66,70	45	19	32	10	0,64
182 123 00	23	1F	68,97	79	69,73	55	19	32	10	0,76
182 124 00	24	1F	72,00	79	72,77	55	19	32	10	0,80
182 125 00	25	1F	75,04	83	75,80	58	19	32	10	0,88
182 126 00	26	1F	78,07	87	78,83	58	19	32	12	0,93
182 127 00	27	1F	81,10	87	81,86	58	19	32	12	0,98
182 128 00	28	1F	84,13	91	84,89	58	19	32	12	1,04
182 130 00	30	1F	90,20	97	90,96	70	19	32	12	1,28
182 132 00	32	1F	96,26	103	97,02	70	19	32	12	1,40
182 133 00	33	1F	99,29	106	100,05	70	19	32	12	1,48
182 134 00	34	1F	102,32	111	103,08	70	19	32	12	1,56
182 135 00	35	1F	105,35	111	106,12	70	19	32	12	1,61
182 136 00	36	1F	108,39	115	109,15	70	19	32	12	1,69
182 140 00	40	1F	120,51	127	121,28	70	19	32	12	2,03
182 144 00	44	1F	132,64	140	133,40	70	19	32	12	2,40
182 148 00	48	1F	144,77	152	145,53	70	19	32	12	2,76
182 150 00	50	4	150,83	-	151,60	70	19	32	14	1,59
182 156 00	56	4	169,02	-	169,79	70	19	32	14	1,71
182 160 00	60	4	181,15	-	181,81	75	19	42	14	2,21
182 172 00	72	4	217,53	-	218,30	75	19	42	14	2,77
182 184 00	84	4	253,92	-	254,68	75	19	42	14	2,96
182 187 00	96	4	290,30	-	291,06	75	19	42	14	3,27

L 075: Pitch 3/8" = 9.525 mm for Timing Belt Width 0.75" = 19.1 mm

Product No.	Number of teeth	Type	De mm	Df mm	d mm	ND mm	b mm	L mm	B mm	Weight kg
182 210 00	10	1F	29,56	36	30,33	20	25,4	38	8	0,14
182 211 00	11	1F	32,59	38	33,35	24	25,4	38	8	0,17
182 212 00	12	1F	35,62	42	36,38	24	25,4	38	8	0,21
182 213 00	13	1F	38,65	44	39,41	28	25,4	38	8	0,26
182 214 00	14	1F	41,68	48	42,45	28	25,4	38	8	0,28
182 215 00	15	1F	44,72	51	45,48	34	25,4	38	8	0,35
182 216 00	16	1F	47,75	54	48,51	36	25,4	38	8	0,40
182 217 00	17	1F	50,78	57	51,54	36	25,4	38	10	0,45
182 218 00	18	1F	53,81	60	54,57	40	25,4	38	10	0,52
182 219 00	19	1F	56,84	63	57,61	40	25,4	38	10	0,58
182 220 00	20	1F	59,88	66	60,64	40	25,4	38	10	0,63
182 221 00	21	1F	62,91	71	63,67	45	25,4	38	10	0,70
182 222 00	22	1F	65,94	75	66,70	45	25,4	38	10	0,78
182 223 00	23	1F	68,97	79	69,73	55	25,4	38	10	0,92
182 224 00	24	1F	72,00	79	72,77	55	25,4	38	10	0,98
182 225 00	25	1F	75,04	83	75,80	58	25,4	38	10	1,07
182 226 00	26	1F	78,07	87	78,83	58	25,4	38	12	1,15
182 227 00	27	1F	81,10	87	81,86	58	25,4	38	12	1,29
182 228 00	28	1F	84,13	91	84,89	58	25,4	38	12	1,43
182 230 00	30	1F	90,20	97	90,96	70	25,4	38	12	1,57
182 232 00	32	1F	96,26	103	97,02	70	25,4	38	12	1,73
182 233 00	33	1F	99,29	106	100,05	70	25,4	38	12	1,84
182 234 00	34	1F	102,32	111	103,08	70	25,4	38	12	1,94
182 235 00	35	1F	105,35	111	106,12	70	25,4	38	12	2,02
182 236 00	36	1F	108,39	115	109,15	70	25,4	38	12	2,12
182 240 00	40	1F	120,51	127	121,28	70	25,4	38	12	2,55
182 244 00	44	1F	132,64	140	133,40	70	25,4	38	12	3,04
182 248 00	48	1F	144,77	152	145,53	70	25,4	38	12	3,54
182 250 00	50	4	150,83	-	151,60	70	25,4	38	14	1,91
182 256 00	56	4	169,02	-	169,79	70	25,4	38	14	2,11
182 260 00	60	4	181,15	-	181,81	75	25,4	45	14	2,59
182 272 00	72	4	217,53	-	218,30	75	25,4	45	14	2,86
182 284 00	84	4	253,92	-	254,68	75	25,4	45	14	3,79
182 287 00	96	4	290,30	-	291,06	75	25,4	45	14	3,76



**Reworking within
24h-service possible.
Custom made parts
on request.**