


AT Pulleys, Pitch 10mm for Taper Bushes



Material: Steel, phosphated.

These steel pulleys offer a much higher wear resistance than standard parts from aluminium. The ready-to-install taper version enables a quick mounting and a fatigue-resistant shaft-to-hub connection.

Taper bushes see page 340.

Ordering Details: e.g.: Product No. 168 773 18, Taper Pulley AT 10, 18 Teeth, Timing Belt Width 25 mm

Profile AT 10, Timing Belt Width 25 mm

Belt Width 25mm	Number of teeth	Type	Outside Ø								Taper Bush Type Page 340	Bore Ø		Weight g
			Pulley mm	Flange mm	d mm	ND mm	Di mm	b mm	L mm	R mm		min. mm	max. mm	
168 773 18	18	16F	55,48	60	57,30	-	37	30	22	8	1008	9	25	356
168 773 19	19	16F	58,66	66	60,48	-	44	30	22	8	1108	9	28	397
168 773 20	20	16F	61,84	66	63,66	-	44	30	22	8	1108	9	28	440
168 773 22	22	16F	68,21	75	70,03	-	50	30	22	8	1108	9	28	532
168 773 24	24	16F	74,57	83	76,39	-	58	30	22	8	1108	9	28	633
168 773 25	25	16F	77,76	83	79,58	-	58	30	22	8	1108	9	28	687
168 773 26	26	16F	80,94	87	82,76	-	63	30	25	5	1610	12	42	742
168 773 27	27	16F	84,12	91	85,94	-	64	30	25	5	1610	12	42	800
168 773 28	28	16F	87,31	93	89,13	-	66	30	25	5	1610	12	42	860
168 773 30	30	16F	93,67	97	95,49	-	68	30	25	5	1610	12	42	988
168 773 32	32	16F	100,04	106	101,86	-	76	30	25	5	1610	12	42	1123
168 773 36	36	10F	112,77	119	114,59	92	-	30	32	2	2012	12	50	1503
168 773 40	40	10F	125,50	131	127,32	96	-	30	32	2	2012	12	50	1854
168 773 44	44	10F	138,24	143	140,06	110	-	30	32	2	2012	12	50	2244
168 773 48	48	10F	150,97	158	152,79	110	-	30	32	2	2012	12	50	2670
168 773 60	60	11F	189,10	200	190,99	110	158	30	32	2	2012	12	50	4168
168 773 72	72	11	227,36	-	229,18	125	200	30	45	15	2517	15	65	5840
168 773 84	84	11	265,56	-	267,38	125	235	30	45	15	2517	15	65	7380
168 773 96	96	11	303,76	-	305,58	125	270	30	45	15	2517	15	65	9000

Profile AT 10, Timing Belt Width 32 mm

Product No. Belt Width 32mm	Number of teeth	Type	Outside Ø								Taper Bush Type Page 340	Bore Ø		Weight g
			Pulley mm	Flange mm	d mm	ND mm	Di mm	b mm	L mm	R mm		min. mm	max. mm	
168 774 18	18	16F	55,48	60	57,30	-	37	38	22	16	1008	9	25	438
168 774 19	19	16F	58,66	66	60,48	-	44	38	22	16	1108	9	28	488
168 774 20	20	16F	61,84	66	63,66	-	44	38	22	16	1108	9	28	540
168 774 22	22	16F	68,21	75	70,03	-	50	38	25	13	1210	10	32	654
168 774 24	24	15F	74,57	83	76,39	-	-	38	38	-	1615	12	42	777
168 774 25	25	15F	77,76	83	79,58	-	-	38	38	-	1615	12	42	844
168 774 26	26	15F	80,94	87	82,76	-	-	38	38	-	1615	12	42	912
168 774 27	27	15F	84,12	91	85,94	-	-	38	38	-	1615	12	42	983
168 774 28	28	15F	87,31	93	89,13	-	-	38	38	-	1615	12	42	1057
168 774 30	30	15F	93,67	97	95,49	-	-	38	38	-	1615	12	42	1214
168 774 32	32	15F	100,04	106	101,86	-	-	38	38	-	1615	12	42	1380
168 774 36	36	16F	112,77	119	114,59	-	86	38	38	6	2012	12	50	1747
168 774 40	40	16F	125,50	131	127,32	-	90	38	38	6	2012	12	50	2155
168 774 44	44	16F	138,24	143	140,06	-	110	38	38	6	2012	12	50	2607
168 774 48	48	10F	150,97	158	152,79	125	-	38	45	7	2517	15	65	3608
168 774 60	60	11F	189,17	200	190,99	125	158	38	45	7	2517	15	65	5633
168 774 72	72	11	227,36	-	229,18	125	200	38	45	7	2517	15	65	6830
168 774 84	84	11	265,56	-	267,38	125	235	38	45	7	2517	15	65	9000
168 774 96	96	11	303,76	-	305,58	125	270	38	45	7	2517	15	65	11270

Taper Clamping Bushes see page 340

These customary conical bushes are used for easy and fast mounting of driving elements in Taper version. They can be used with or without key.

The bushes are available with various outer dimensions. For every outside measure there are bushes with many different bores available. This mounting method is cost-efficient and fast, and suitable for rather high torques.

