


## Pevné rukoväte DIN 39 ST

Materiál: Oceľ, pozinkovaná.

Verzia E = so závitovou skrutkou a imbus hlavou.



Informácie potrebné na objednanie: napr.: Produkt č. 662 110 00, Rukoväť DIN 39 ST, Verzia E 10 mm


Produkt č. Verzia E	d <sub>1</sub> mm	d <sub>3</sub> mm	d <sub>4</sub> <sup>h13</sup> mm	l <sub>1</sub> mm	l <sub>2</sub> mm	l <sub>3</sub> mm	s mm	Hmotnosť g
662 110 00	10	M4	7	32	7	4	-*	11
662 113 00	13	M5	8	40	9	5	-*	24
662 116 00	16	M6	10	50	11	7	3	45
662 120 00	20	M8	13	64	13	8	4	91
662 125 00	25	M10	16	80	14	10	5	177
662 132 00	32	M12	20	100	21	13	6	360
662 136 00	36	M16	22	112	26	14	8	526

\*nie podľa DIN 39.

## Pevné rukoväte DIN 39 TH

Materiál: Plast Termoplast (Polyamid), čierny, matný.

Verzia E = so závitovou skrutkou a imbus hlavou.




Informácie potrebné na objednanie: napr.: Produkt č. 662 220 00, Rukoväť DIN 39 TH, Verzia E 20 mm

Produkt č. Verzia E	d <sub>1</sub> mm	d <sub>3</sub> mm	d <sub>4</sub> <sup>h13</sup> mm	l <sub>1</sub> mm	l <sub>2</sub> mm	l <sub>3</sub> mm	s mm	Hmotnosť g
662 220 00	20	M8	13	64	13	8	4	25
662 225 00	25	M10	16	80	14	10	5	50
662 232 00	32	M12	20	100	21	13	6	100

## Pevné rukoväte DIN 39 AL

Materiál: Leštený hliník.

Verzia E = s odliatou závitovou skrutkou a imbus hlavou.



Informácie potrebné na objednanie: napr.: Produkt č. 662 316 00, Rukoväť DIN 39 AL, Verzia E 16 mm

Produkt č. Verzia E	d <sub>1</sub> mm	d <sub>3</sub> mm	d <sub>4</sub> <sup>h13</sup> mm	l <sub>1</sub> mm	l <sub>2</sub> mm	l <sub>3</sub> mm	s mm	Hmotnosť g
662 316 00	16	M6	10	50	10*	7	3	20
662 320 00	20	M8	13	64	12*	8	4	35
662 325 00	25	M10	16	80	16*	12*	5	85
662 332 00	32	M12	20	100	21*	16*	6	150
662 336 00	36	M16	22	112	25*	16*	8	210

\*nie podľa DIN 39.