


## Elbow Banjo Assembly with Sealing Ring

Material: Brass, nickel-plated.




Ordering details: e.g.: Product No. 86350405, Elbow Banjo Assembly with Sealing Ring, Tube Outer-Ø 4 mm, Thread M5

Product No.	Ø A mm	B	D mm	D1 mm	SW mm	Ø F mm	G mm	Weight g
863 504 05	4	M5	18,7	22	8	9,5	4,0	13
863 504 18	4	G <sup>1</sup> / <sub>8</sub> A	20,6	30	14	11,0	6,0	34
863 506 05	6	M5	22,2	22	8	12,5	4,0	17
863 506 28	6	G <sup>1</sup> / <sub>4</sub> A	24,2	34	17	13,0	7,4	54
863 508 18	8	G <sup>1</sup> / <sub>8</sub> A	23,7	30	14	14,0	6,0	37
863 508 28	8	G <sup>1</sup> / <sub>4</sub> A	24,7	34	17	14,0	7,4	56
863 510 28	10	G <sup>1</sup> / <sub>4</sub> A	30,2	34	17	16,0	7,4	59


## Elbow Banjo Assembly, Regulating Out, with Sealing Ring

Material: Brass, nickel-plated.

Symbol



Ordering details: e.g.: Product No. 86360405, Elbow Banjo Assembly, Regulating Out, with Sealing Ring, Tube Outer-Ø 4 mm, Thread M5




Product No.	Ø A mm	B	D mm	D1 mm	SW mm	Ø F mm	G mm	Weight g
863 604 05	4	M5	18,7	27,0	8	9,5	4,4	13
863 604 18	4	G <sup>1</sup> / <sub>8</sub> A	20,6	34,0	14	11,0	6,0	34
863 606 05	6	M5	22,2	27,0	8	12,5	4,4	17
863 606 18	6	G <sup>1</sup> / <sub>8</sub> A	23,7	34,0	14	12,5	6,0	37
863 606 28	6	G <sup>1</sup> / <sub>4</sub> A	24,2	36,5	17	13,0	6,0	58
863 608 28	8	G <sup>1</sup> / <sub>4</sub> A	24,7	36,5	17	14,0	6,0	59
863 608 38	8	G <sup>3</sup> / <sub>8</sub> A	26,7	51,5	22	16,5	10,0	123
863 608 18	8	G <sup>1</sup> / <sub>8</sub> A	23,7	34,0	14	13,5	6,0	39
863 610 28	10	G <sup>1</sup> / <sub>4</sub> A	30,2	36,5	17	15,7	6,0	63

## Banjo Bolts with Sealing Rings

Materials: Brass, nickel-plated.

For combination with banjo bodies.



Ordering details: e.g.: Product No. 86470018, Banjo Bolt with Sealing Rings, G<sup>1</sup>/<sub>8</sub>A

Product No.	B	D1 mm	SW mm	Ø S mm	Weight g
864 700 18	G <sup>1</sup> / <sub>8</sub> A	30	14	5,0	15
864 700 28	G <sup>1</sup> / <sub>4</sub> A	31,5	17	8,5	25
864 700 38	G <sup>3</sup> / <sub>8</sub> A	41	22	10,0	60