


V-Belt Pulleys for Taper Bushes, Profile Z, SPZ and XPZ (10), 2 Grooves



Material: cast iron EN-GJL-250, phosphated.

V-belt pulleys for taper bushes, for easy and fast mounting. The taper bush has to be ordered separately.

Regarding DIN 2211, DIN 2217 and ISO 4183, matching to classical V-belts DIN 2215 and narrow V-belts DIN 7753-1 / ISO 4184. Also suitable for V-belts 3V/9N according to ARPM/MPTA. The nominal diameter D_1 is the datum diameter.

Ordering Details: e.g.: Product No. MAE 151-Z-2-50, V-Belt Pulley for Taper Clamping Bush, Profile Z, 2 Grooves, Nominal Diameter 50 mm

Product No. Profile Z, SPZ, XPZ	No. of Grooves	Nominal Ø		Design	fitting Bush No.	Bore mm	E mm	h mm	J mm	K mm	L mm	M mm	N mm	Weight kg
		D_1 mm	D_A mm											
MAE 151-Z-2-50	2	50 ¹⁾³⁾	54	9	1008	9 - 25	-	50	26	25	25	-	-	0,50
MAE 151-Z-2-56	2	56 ²⁾³⁾	60	9	1008	9 - 25	-	49	32	27	22	-	-	0,50
MAE 151-Z-2-60	2	60 ²⁾	64	9	1108	9 - 28	-	49	36	27	22	-	-	0,50
MAE 151-Z-2-63	2	63	67	8	1108	9 - 28	-	28	40	6	22	-	-	0,30
MAE 151-Z-2-67	2	67	71	8	1108	9 - 28	-	28	42	6	22	-	-	0,38
MAE 151-Z-2-71	2	71	75	8	1108	9 - 28	-	28	42	6	22	-	-	0,50
MAE 151-Z-2-75	2	75	79	8	1210	10 - 32	-	28	51	3	25	-	-	0,43
MAE 151-Z-2-80	2	80	84	8	1210	10 - 32	-	28	51	3	25	-	-	0,52
MAE 151-Z-2-85	2	85	89	8	1610	12 - 42	-	28	60	3	25	-	-	0,50
MAE 151-Z-2-90	2	90	94	8	1610	12 - 42	-	28	61	3	25	-	-	0,65
MAE 151-Z-2-95	2	95	99	8	1610	12 - 42	-	28	66	3	25	-	-	1,00
MAE 151-Z-2-100	2	100	104	8	1610	12 - 42	-	28	71	3	25	-	-	0,90
MAE 151-Z-2-106	2	106	110	8	1610	12 - 42	-	28	76	3	25	-	-	1,08
MAE 151-Z-2-112	2	112	116	8	1610	12 - 42	-	28	83	3	25	-	-	1,20
MAE 151-Z-2-118	2	118	122	8	1610	12 - 42	-	28	90	3	25	-	-	1,50
MAE 151-Z-2-125	2	125	129	8	1610	12 - 42	-	28	96	3	25	-	-	1,50
MAE 151-Z-2-132	2	132	136	8	1610	12 - 42	-	28	103	3	25	-	-	2,00
MAE 151-Z-2-140	2	140	144	8	1610	12 - 42	-	28	111	3	25	-	-	2,20
MAE 151-Z-2-150	2	150	154	1	2012	12 - 50	-	28	-	-	32	4	112	3,00
MAE 151-Z-2-160	2	160	164	1	2012	12 - 50	-	28	-	-	32	4	112	2,50
MAE 151-Z-2-170	2	170	174	1	2012	12 - 50	-	28	-	-	32	4	112	1,50
MAE 151-Z-2-180	2	180	184	14	2012	12 - 50	6	28	152	-	32	4	112	2,80
MAE 151-Z-2-190	2	190	194	14	2012	12 - 50	12	28	162	-	32	4	112	3,50
MAE 151-Z-2-200	2	200	204	14	2012	12 - 50	6	28	171	-	32	4	112	3,30
MAE 151-Z-2-224	2	224	228	13	2012	12 - 50	15	28	195	-	32	4	112	4,00
MAE 151-Z-2-250	2	250	254	4	2012	12 - 50	-	28	221	2	32	2	112	4,40
MAE 151-Z-2-280	2	280	284	4	2012	12 - 50	-	28	251	2	32	2	112	5,00
MAE 151-Z-2-315	2	315	319	4	2012	12 - 50	-	28	286	2	32	2	112	5,90
MAE 151-Z-2-355	2	355	359	4	2012	12 - 50	-	28	326	2	32	2	112	7,80
MAE 151-Z-2-400	2	400	404	4	2517	15 - 65	-	28	371	8,5	45	8,5	124	9,50
MAE 151-Z-2-450	2	450	454	4	2517	15 - 65	-	28	421	8,5	45	8,5	124	10,40
MAE 151-Z-2-500	2	500	504	4	2517	15 - 65	-	28	471	8,5	45	8,5	124	12,75


1) Not for V-belts SPZ, XPZ and 3V/9N.

2) Not for V-belts SPZ and 3V/9N.

3) Steel C45, phosphated.


Taper Bushes

The bushes are available with various outer dimensions. For every outside measure there are bushes with many different bores available. They can be used with and without key.



Mounting

Videos are available on our homepage and on YouTube. The instructions are available as a PDF file in the online shop and on paper in the scope of delivery of the bush.



D www.maedler.de
A www.maedler.at
CH www.maedler.ch