


V-Belt Pulleys for Taper Bushes, Profile A, SPA and XPA (13), 2 Grooves



Material: cast iron EN-GJL-250, phosphated.

V-belt pulleys for taper bushes, for easy and fast mounting. The taper bush has to be ordered separately.

Regarding DIN 2211, DIN 2217 and ISO 4183, matching to classical V-belts DIN 2215 and narrow V-belts DIN 7753-1 / ISO 4184. The nominal diameter D_1 is the datum diameter.

Ordering Details: e.g.: Product No. MAE 151-A-2-63, V-Belt Pulley for Taper Clamping Bush, Profile A, 2 Grooves, Nominal Diameter 63 mm

Product No. Profile A, SPA, XPA	No. of Grooves	Nominal Ø		Design	fitting Bush No.	Bore mm	E mm	h mm	J mm	K mm	L mm	M mm	N mm	Weight kg
		D_1 mm	D_A mm											
MAE 151-A-2-63	2	63 ¹⁾³⁾	68,5	8	1008	9 - 25	-	35	32,5	13	22	-	-	0,42
MAE 151-A-2-67	2	67 ¹⁾	72,5	8	1108	9 - 28	-	35	37	13	22	-	-	0,44
MAE 151-A-2-71	2	71 ²⁾	76,5	8	1108	9 - 28	-	35	40	13	22	-	-	0,50
MAE 151-A-2-75	2	75 ²⁾	80,5	8	1108	9 - 28	-	35	44	13	22	-	-	0,59
MAE 151-A-2-80	2	80 ²⁾	85,5	8	1210	10 - 32	-	35	50	10	25	-	-	0,58
MAE 151-A-2-85	2	85 ²⁾	90,5	8	1210	10 - 32	-	35	55	10	25	-	-	0,75
MAE 151-A-2-90	2	90	95,5	8	1610	12 - 42	-	35	59	10	25	-	-	0,71
MAE 151-A-2-95	2	95	100,5	8	1610	12 - 42	-	35	63	10	25	-	-	0,85
MAE 151-A-2-100	2	100	105,5	8	1610	12 - 42	-	35	66	10	25	-	-	0,96
MAE 151-A-2-106	2	106	111,5	8	1610	12 - 42	-	35	72	10	25	-	-	1,20
MAE 151-A-2-112	2	112	117,5	8	1610	12 - 42	-	35	78	10	25	-	-	1,38
MAE 151-A-2-118	2	118	123,5	8	1610	12 - 42	-	35	84	10	25	-	-	1,58
MAE 151-A-2-125	2	125	130,5	8	1610	12 - 42	-	35	91	10	25	-	-	1,88
MAE 151-A-2-132	2	132	137,5	8	2012	12 - 50	-	35	98	3	32	-	-	2,07
MAE 151-A-2-140	2	140	145,5	8	2012	12 - 50	-	35	106	3	32	-	-	2,50
MAE 151-A-2-150	2	150	155,5	8	2012	12 - 50	-	35	116	3	32	-	-	2,99
MAE 151-A-2-160	2	160	165,5	8	2012	12 - 50	-	35	125	3	32	-	-	3,50
MAE 151-A-2-170	2	170	175,5	8	2012	12 - 50	-	35	135	3	32	-	-	3,20
MAE 151-A-2-180	2	180	185,5	6	2012	12 - 50	10	35	146	1,5	32	1,5	108	4,00
MAE 151-A-2-190	2	190	195,5	6	2012	12 - 50	10	35	156	1,5	32	1,5	108	3,66
MAE 151-A-2-200	2	200	205,5	7	2517	15 - 65	10	35	165	5	45	5	123	4,74
MAE 151-A-2-212	2	212	217,5	7	2517	15 - 65	18	35	177	5	45	5	123	5,22
MAE 151-A-2-224	2	224	229,5	13	2517	15 - 65	18	35	189	-	45	10	124	5,45
MAE 151-A-2-236	2	236	241,5	14	2517	15 - 65	12	35	202	-	45	10	124	5,74
MAE 151-A-2-250	2	250	255,5	4	2517	15 - 65	12	35	215	5	45	5	124	5,65
MAE 151-A-2-280	2	280	285,5	13	2517	15 - 65	12	35	245	-	45	10	124	6,20
MAE 151-A-2-300	2	300	305,5	14	2517	15 - 65	12	35	265	-	45	10	124	6,86
MAE 151-A-2-315	2	315	320,5	13	2517	15 - 65	12	35	280	-	45	10	124	7,17
MAE 151-A-2-355	2	355	360,5	13	2517	15 - 65	-	35	320	-	45	10	124	7,79
MAE 151-A-2-400	2	400	405,5	13	2517	15 - 65	-	35	365	-	45	10	124	9,89
MAE 151-A-2-450	2	450	455,5	13	2517	15 - 65	-	35	465	-	45	10	124	11,02
MAE 151-A-2-500	2	500	505,5	13	2517	15 - 65	-	35	525	-	45	10	125	13,10
MAE 151-A-2-630	2	630	635,5	4	3020	20 - 75	-	35	595	8	51	18	159	18,50


¹⁾ Not for V-belts SPA and XPA.

²⁾ Not for V-belts SPA.

³⁾ Steel C45, phosphated.



Taper Bushes

The bushes are available with various outer dimensions. For every outside measure there are bushes with many different bores available. They can be used with and without key.



Mounting

Videos are available on our homepage and on YouTube. The instructions are available as a PDF file in the online shop and on paper in the scope of delivery of the bush.



D www.maedler.de
A www.maedler.at
CH www.maedler.ch