

## Premium Rostschutz-Öl Spray

Print date 17.03.2023
Revision date 17.03.2023
Version 6.0 (en)

replaces version of 17.11.2021 (5.1)

## \* SECTION 1: Identification of the substance/mixture and of the company/undertaking

#### \* 1.1 Product identifier

**Trade name/designation** Premium Rostschutz-Öl Spray **Unique Formula Identifier** UFI: T8SR-9E4M-200F-UUA8

## **Hazard components**

Kerosin (Erdöl), hydrodesulfuriertes; Kerosin - nicht spezifiziert (Kopie)

#### 1.2 Relevant identified uses of the substance or mixture and uses advised against

#### Use of the substance/mixture

corrosion prevention

Preservation of metal, wood, leather, rubber, synthetic material

## 1.3 Details of the supplier of the safety data sheet

#### Manufacturer

F.W.Klever
Hauptstraße 20
D-84168 Aham
Telephone +49 (0) 8744 96 99 10
Telefax + 49 (0) 8744 96 99 96
E-mail info@ballistol.de
Website www.ballistol.de

Department responsible for information:

Qualitätssicherung

Telephone +49 (0) 8744 96 99 80

E-mail (competent person):

info@ballistol.de

## \* 1.4 Emergency telephone number

Emergency CONTACT (24-Hour-Number): GBK GmbH +49 (0)6132-84463

## **SECTION 2: Hazards identification**

## 2.1 Classification of the substance or mixture

Classification according to Regulation (EC) No 1272/2008

Classification procedure

[CLP]

Aerosol 1, H222 H229 Aquatic Chronic 3, H412

#### Hazard statements for physical hazards

H222 Extremely flammable aerosol.

H229 Pressurised container: May burst if heated.

## Hazard statements for environmental hazards

H412 Harmful to aquatic life with long lasting effects.

## 2.2 Label elements

#### Labelling according to Regulation (EC) No. 1272/2008 [CLP]

#### **Hazard components**

Kerosin (Erdöl), hydrodesulfuriertes ; Kerosin - nicht spezifiziert (Kopie)



## Premium Rostschutz-Öl Spray

Print date 17.03.2023 Revision date 17.03.2023 Version 6.0 (en)

replaces version of 17.11.2021 (5.1)

#### Hazard pictograms



## Signal word

Danger

## **Hazard statements**

H222 Extremely flammable aerosol.

H229 Pressurised container: May burst if heated.

H412 Harmful to aquatic life with long lasting effects.

## **Precautionary statements**

P102 Keep out of reach of children.

P251 Do not pierce or burn, even after use.

P210 Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.

P273 Avoid release to the environment.

P410 + P412 Protect from sunlight. Do not expose to temperatures exceeding 50 °C/122 °F.

P501 Dispose of contents/container to recycling

## 2.3 Other hazards

No data available

## **SECTION 3: Composition / information on ingredients**

#### 3.1 Substances

not applicable

#### 3.2 Mixtures

## Hazardous ingredients

CAS No.	EC No.	Substance name	Concentration	Classification according to Regulation (EC) No 1272/2008 [CLP]	SCL/ M/ ATE
		Kerosin (Erdöl), hydrodesulfuriertes ; Kerosin - nicht spezifiziert (Kopie)	25 weight-%	Asp. Tox. 1; H304	
106-97-8	203-448-7	butane	> 15 weight-%	Flam. Gas 1; H220 Press. Gas	
74-98-6	200-827-9	propane	9 weight-%	Flam. Gas 1; H220 Press. Gas	

## **SECTION 4: First aid measures**

## 4.1 Description of first aid measures

## Following inhalation

Provide fresh air.

In the event of symptoms refer for medical treatment.

## Following skin contact

After contact with skin, wash immediately with plenty of water and soap.



## Premium Rostschutz-Öl Spray

Print date 17.03.2023 Revision date 17.03.2023 Version 6.0 (en)

replaces version of 17.11.2021 (5.1)

#### After eye contact

After contact with the eyes, rinse with water with the eyelids open for a sufficient length of time, then consult an ophthalmologist immediately.

#### Following ingestion

If swallowed, immediately drink:

Water

Seek medical advice immediately.

## 4.2 Most important symptoms and effects, both acute and delayed

No data available

#### 4.3 Indication of any immediate medical attention and special treatment needed

#### Notes for the doctor

Treat symptomatically.

## **SECTION 5: Firefighting measures**

#### 5.1 Extinguishing media

## Suitable extinguishing media

Foam ABC-powder Carbon dioxide (CO2) Water spray jet

## Unsuitable extinguishing media

Full water jet

## 5.2 Special hazards arising from the substance or mixture

#### **Hazardous combustion products**

In the event of fire the following can be released: Nitrogen oxides (NOx) Carbon dioxid (CO2)

#### 5.3 Advice for firefighters

## Special protective equipment for firefighters

In case of fire: Wear self-contained breathing apparatus.

#### **Additional information**

Use water spray jet to protect personnel and to cool endangered containers.

Heating causes rise in pressure with risk of bursting

Fire residues and contaminated firefighting water must be disposed of in accordance with the local regulations.

## **SECTION 6: Accidental release measures**

#### 6.1 Personal precautions, protective equipment and emergency procedures

## For non-emergency personnel

Remove all sources of ignition.

Wear breathing apparatus if exposed to vapours/dusts/aerosols.

Special danger of slipping by leaking/spilling product.



## Premium Rostschutz-Öl Spray

Print date 17.03.2023 Revision date 17.03.2023 Version 6.0 (en)

replaces version of 17.11.2021 (5.1)

#### 6.2 Environmental precautions

Do not allow to enter into surface water or drains.

## 6.3 Methods and material for containment and cleaning up

#### For containment

Take up residues with absorbent material (e.g. sawdust).

#### For cleaning up

Clean contaminated articles and floor according to the environmental legislation.

#### 6.4 Reference to other sections

No data available

## **SECTION 7: Handling and storage**

#### 7.1 Precautions for safe handling

#### **Protective measures**

If local exhaust ventilation is not possible or not sufficient, the entire working area should be ventilated by technical means.

Do not spray on naked flames or any incandescent material.

Keep away from sources of ignition - No smoking.

Protect aerosols from temperatures exceeding 50°C/ 122°F

Do not inhale gases/vapours/aerosols.

#### Advices on general occupational hygiene

Remove contaminated, saturated clothing immediately.

Wash hands before breaks and after work.

## 7.2 Conditions for safe storage, including any incompatibilities

#### Requirements for storage rooms and vessels

Keep/Store only in original container.

#### Storage class

2B Aerosol dispensers and lighters

## Further information on storage conditions

Recommended storage temperature: room temperature.

Storage time: 3 years.

## 7.3 Specific end use(s)

No data available

## **SECTION 8: Exposure controls/personal protection**

## 8.1 Control parameters

#### Occupational exposure limit values

CAS No.	EC No.	Substance name	occupational exposure limit value
106-97-8	203-448-7	n-Butane	600 [ml/m³(ppm)] 1450 [mg/m³]

Short-term(ml/m³) 750 Short-term(mg/m³) 1810

(UK)



## Premium Rostschutz-Öl Spray

Print date 17.03.2023
Revision date 17.03.2023
Version 6.0 (en)

replaces version of 17.11.2021 (5.1)

CAS No. EC No. Substance name occupational exposure limit value

106-97-8 203-448-7 n-Butane Short-term(ml/m³) 1000 (1)
(1) 15 minutes average value
(IE)

#### 8.2 Exposure controls

## Personal protection equipment

## Eye/face protection

With demand: protective glasses

## **Hand protection**

Gloves (oil-resistant)

Recommendation: protective glove (referred to EN374).

## **Respiratory protection**

Respiratory protection must be worn whenever the WEL levels have been exceeded

The following applies to propane in general: If the concentration is exceeded, closed-circuit breathing apparatures must be used

Use filter apparatus type AX, identification colour brown according to EN 371

## \* SECTION 9: Physical and chemical properties

## \* 9.1 Information on basic physical and chemical properties

#### **Physical state**

Aerosol

## Colour

light yellow

## Odour

characteristic

## Safety relevant basis data

	Value	Method	Source, Remark
Odour threshold:	not determined		
Melting point/freezing point	not determined		
Boiling point or initial boiling point and boiling range	-48 °C		(Propan)
flammability	not determined		
Lower and upper explosion limit	Upper explosion limit 10.9 Vol-%		(Propan)
Lower and upper explosion limit	Lower explosion limit approx. 1.5 Vol-%		(Propan)
Flash point	approx104 °C		(Propan)
Auto-ignition temperature	not determined		
Decomposition temperature	not determined		
pH	in delivery state approx. 8		emulsion in water
Viscosity	Kinematic viscosity approx. 28 mm²/s (20°C)		information concerns to liquid phase



Premium Rostschutz-Öl Spray

Print date 17.03.2023
Revision date 17.03.2023
Version 6.0 (en)

replaces version of 17.11.2021 (5.1)

	Value	Method	Source, Remark
Solubility(ies)	Water solubility (20°C) pressure 1013 hPa		Immiscible
Partition coefficient n- octanol/water (log value)	not determined		
Vapour pressure	not determined		
Density and/or relative density	approx. 0.874 g/mL (20°C) pressure 1013 hPa		information concerns to liquid phase
Relative vapour density	not determined		
particle characteristics	not determined		
Other information			
her safety characteristics			
-	Value	Method	Source, Remark
refraction index	approx. 1.48 (20°C)		

## **SECTION 10: Stability and reactivity**

#### 10.1 Reactivity

No data available

## 10.2 Chemical stability

No data available

## 10.3 Possibility of hazardous reactions

No data available

#### 10.4 Conditions to avoid

Container under pressure. Protect from direct exposure to sunlight and temperatures exceeding 50°C/122°F.

## 10.5 Incompatible materials

Oxidising agent, strong

## 10.6 Hazardous decomposition products

Carbon monoxide Carbon dioxide

#### **Additional information**

Product is stable under normal storage conditions

## **SECTION 11: Toxicological information**

## 11.1 Information on hazard classes as defined in Regulation (EC) No 1272/2008

## **Acute toxicity**

## **Animal data**

	Effective dose	Method,Evaluation	Source, Remark
Acute oral toxicity	> 2000 mg/kg Species Rat		Data apply to the main component.



## ES WIRKT.

Acute dermal toxicity

# Safety Data Sheet according to Regulation (EC) No. 1907/2006 (REACH)

Source, Remark

## Premium Rostschutz-Öl Spray

Print date 17.03.2023
Revision date 17.03.2023
Version 6.0 (en)

Method, Evaluation

replaces version of 17.11.2021 (5.1)

Effective dose

> 3000 mg/kg Species Rabbit

Acute inhalation toxicity not determined

Skin corrosion/irritation

not determined

Serious eye damage/irritation

**Animal data** 

Result / Evaluation Method Source, Remark

slightly irritant

Sensitisation to the respiratory tract

not determined

Skin sensitisation

**Animal data** 

Result / Evaluation Dose / Concentration Method Source, Remark

not sensitising.

Germ cell mutagenicity

not determined

Carcinogenicity
not determined

Reproductive toxicity

not determined

STOT-single exposure

not determined

STOT-repeated exposure

not determined

**Aspiration hazard** 

not determined

11.2 Information on other hazards

No data available

## **SECTION 12: Ecological information**

## 12.1 Toxicity

## **Aquatic toxicity**

	Effective dose	Method,Evaluation	Source, Remark
Acute (short-term) fish toxicity	not determined		
Chronic (long-term) fish toxicity	not determined		
Acute (short-term) toxicity to crustacea	not determined		
Chronic (long-term) toxicity to aquatic invertebrate	not determined		
Acute (short-term) toxicity to algae and cyanobacteria	not determined		



ES WIRKT.

## Safety Data Sheet according to Regulation (EC) No. 1907/2006 (REACH)

Source, Remark

## Premium Rostschutz-Öl Spray

Print date 17.03.2023 Revision date 17.03.2023 Version 6.0 (en)

Method, Evaluation

replaces version of 17.11.2021 (5.1)

Effective dose

Chronic (long-term) toxicity to aquatic algae and

cyanobacteria

Toxicity to other aquatic plants/organisms

not determined

not determined

Toxicity to microorganisms not determined

## 12.2 Persistence and degradability

Value Method Source. Remark Biodegradation Moderately/partially biodegradable.

## 12.3 Bioaccumulative potential

No data available

## 12.4 Mobility in soil

No data available

## 12.5 Results of PBT and vPvB assessment

No data available

## 12.6 Endocrine disrupting properties

No data available

#### 12.7 Other adverse effects

No data available

## **SECTION 13: Disposal considerations**

#### 13.1 Waste treatment methods

#### Waste codes/waste designations according to EWC/AVV

Waste code product Waste name

130205 \* mineral-based non-chlorinated engine, gear and lubricating oils

## Appropriate disposal / Package

Non-contaminated packages may be recycled.

Recycle sales packaging via DSD (Duales System Deutschland).

## **SECTION 14: Transport information**

	Land transport (ADR/RID)	Sea transport (IMDG)	Air transport (ICAO-TI / IATA- DGR)
14.1 UN number or ID number	UN 1950	UN 1950	UN 1950
14.2 UN proper shipping name	AEROSOLS	AEROSOLS	Aerosols, flammable
14.3 Transport hazard class(es)	2.1	2.1	2.1
14.4 Packing group	-	-	-
14.5 Environmental hazards	No	No	No



## Premium Rostschutz-Öl Spray

Print date 17.03.2023 Revision date 17.03.2023 Version 6.0 (en)

replaces version of 17.11.2021 (5.1)

## 14.6 Special precautions for user

No data available

## 14.7 Maritime transport in bulk according to IMO instruments

No data available

#### Land transport (ADR/RID)

UN number or ID number UN 1950 UN proper shipping name AEROSOLS

Transport hazard class(es) 2.1
Hazard label(s) 2.1
Classification code 5F
Packing group Environmental hazards No
Limited quantity (LQ) 1 L

Special provisions 190, 327, 344, 625

Tunnel restriction code D

## Sea transport (IMDG)

UN number or ID number UN 1950 UN proper shipping name AEROSOLS

Transport hazard class(es) 2.1
Packing group Environmental hazards No
Limited quantity (LQ) 1 L
Marine pollutant No
EmS F-D, S-U

## Air transport (ICAO-TI / IATA-DGR)

UN number or ID number UN 1950

UN proper shipping name Aerosols, flammable

Transport hazard class(es) 2.1
Packing group Environmental hazards No

## **SECTION 15: Regulatory information**

## 15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture

No data available

#### 15.2 Chemical Safety Assessment

For this substance a chemical safety assessment is not required.



## Premium Rostschutz-Öl Spray

Print date 17.03.2023
Revision date 17.03.2023
Version 6.0 (en)

replaces version of 17.11.2021 (5.1)

#### **SECTION 16: Other information**

#### **Additional information**

National and local regulations concerning chemicals shall be observed.

The above information describes exclusively the safety requirements of the product and is based on our present-day knowledge. The information is intended to give you advice about the safe handling of the product named in this safety data sheet, for storage, processing, transport and disposal. The information cannot be transferred to other products. In the case of mixing the product with other products or in the case of processing, the information on this safety data sheet is not necessarily valid for the new made-up material.

## Relevant H- and EUH-phrases (Number and full text)

H220 Extremely flammable gas.

H304 May be fatal if swallowed and enters airways.

## Indication of changes

\* Data changed compared with the previous version