(B) (RL

Page 1 of 19

Safety data sheet according to Regulation (EC) No 1907/2006, Annex II

Revision date / version: 26.09.2022 / 0016

Replacing version dated / version: 01.11.2021 / 0015

Valid from: 26.09.2022 PDF print date: 30.03.2023

WD-40® Specialist® High Performance PTFE Lubricant

WD-40® SPECIALIST® PTFE

# Safety data sheet according to Regulation (EC) No 1907/2006, Annex II

# SECTION 1: Identification of the substance/mixture and of the company/undertaking

#### 1.1 Product identifier

# WD-40® Specialist® High Performance PTFE Lubricant WD-40® SPECIALIST® PTFE

# 1.2 Relevant identified uses of the substance or mixture and uses advised against Relevant identified uses of the substance or mixture:

Lubricant

#### **Uses advised against:**

No information available at present.

#### 1.3 Details of the supplier of the safety data sheet

(GB)

WD-40 Company Limited PO Box 440 GB-Kiln Farm, Milton Keynes, MK11 3LF

Tel.: +44 (0) 1908 555400 Fax: +44 (0) 1908 266900 E-Mail: Compliance@wd40.co.uk Homepage: www.wd40.co.uk

WD-40 Company Limited Noorderpoort 93E NL- 5916PJ Venlo

Tel.: +31 85 487 46 91

WD-40 Company Limited, 252 Upper Third Street, Milton Keynes, MK9 1DZ +44 (0)1908 555450

Qualified person's e-mail address: info@chemical-check.de, k.schnurbusch@chemical-check.de Please DO NOT use for requesting Safety Data Sheets.

# 1.4 Emergency telephone number

# Emergency information services / official advisory body:

(RL

National Poisons Information Centre, Beaumont Hospital, Dublin 9, Ireland, Tel.: +353 (0)1 809 2166 (Public Poisons Info Line, 8am-10pm, 7 days a week) +353 (0)1 809 2566 (Info for Healthcare Professionals ONLY, 24 h, 7 days a week)

#### Telephone number of the company in case of emergencies:

+44 20 3807 3798

#### **SECTION 2: Hazards identification**

2.1 Classification of the substance or mixture
Classification according to Regulation (EC) 1272/2008 (CLP)
Hazard class Hazard category Hazard statement



#### Page 2 of 19

Safety data sheet according to Regulation (EC) No 1907/2006, Annex II

Revision date / version: 26.09.2022 / 0016

Replacing version dated / version: 01.11.2021 / 0015

Valid from: 26.09.2022 PDF print date: 30.03.2023

WD-40® Specialist® High Performance PTFE Lubricant

WD-40® SPECIALIST® PTFE

Skin Irrit. H315-Causes skin irritation.

H304-May be fatal if swallowed and enters airways. Asp. Tox. 1

STOT SE 3 H336-May cause drowsiness or dizziness.

2 Aquatic Chronic H411-Toxic to aquatic life with long lasting effects.

Aerosol 1 H222-Extremely flammable aerosol.

Aerosol H229-Pressurised container: May burst if heated.

#### 2.2 Label elements

# Labeling according to Regulation (EC) 1272/2008 (CLP)



Danger

H315-Causes skin irritation. H336-May cause drowsiness or dizziness. H411-Toxic to aquatic life with long lasting effects. H222-Extremely flammable aerosol. H229-Pressurised container: May burst if heated.

P101-If medical advice is needed, have product container or label at hand. P102-Keep out of reach of children.

P210-Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking. P211-Do not spray on an open flame or other ignition source. P251-Do not pierce or burn, even after use. P261-Avoid breathing vapours or spray. P273-Avoid release to the environment. P280-Wear protective gloves.

P312-Call a POISON CENTRE / doctor if you feel unwell.

P405-Store locked up. P410+P412-Protect from sunlight. Do not expose to temperatures exceeding 50 °C.

P501-Dispose of contents / container to an approved waste disposal facility.

Without adequate ventilation, formation of explosive mixtures may be possible.

Hydrocarbons, C9-C11, n-alkanes, isoalkanes, cyclics, <2% aromatics

Hydrocarbons, C7, n-alkanes, isoalkanes, cyclics

Hydrocarbons, C7-C9, isoalkanes

#### 2.3 Other hazards

The mixture does not contain any vPvB substance (vPvB = very persistent, very bioaccumulative) or is not included under XIII of the regulation (EC) 1907/2006 (< 0,1 %).

The mixture does not contain any PBT substance (PBT = persistent, bioaccumulative, toxic) or is not included under XIII of the regulation (EC) 1907/2006 (< 0,1 %).

The mixture does not contain any substance with endocrine disrupting properties (< 0,1 %).

# **SECTION 3: Composition/information on ingredients**

#### Aerosol

#### 3.1 Substances

# n.a. 3.2 Mixtures

Hydrocarbons, C7, n-alkanes, isoalkanes, cyclics	
Registration number (REACH)	01-2119475515-33-XXXX
Index	
EINECS, ELINCS, NLP, REACH-IT List-No.	927-510-4
CAS	
content %	25-<40
EINECS, ELINCS, NLP, REACH-IT List-No. CAS	927-510-4



Page 3 of 19

Safety data sheet according to Regulation (EC) No 1907/2006, Annex II

Revision date / version: 26.09.2022 / 0016

Replacing version dated / version: 01.11.2021 / 0015

Valid from: 26.09.2022 PDF print date: 30.03.2023

WD-40® Specialist® High Performance PTFE Lubricant

WD-40® SPECIALIST® PTFE

Classification according to Regulation (EC) 1272/2008 (CLP), M-	Flam. Liq. 2, H225
factors	Skin Irrit. 2, H315
	STOT SE 3, H336
	Asp. Tox. 1, H304
	Aquatic Chronic 2, H411

Hydrocarbons, C9-C11, n-alkanes, isoalkanes, cyclics, <2% aromatics	
Registration number (REACH)	01-2119463258-33-XXXX
Index	
EINECS, ELINCS, NLP, REACH-IT List-No.	919-857-5
CAS	
content %	20-<30
Classification according to Regulation (EC) 1272/2008 (CLP), M-	EUH066
factors	Flam. Liq. 3, H226
	STOT SE 3, H336
	Asp. Tox. 1, H304

Hydrocarbons, C7-C9, isoalkanes	
Registration number (REACH)	01-2119471305-42-XXXX
Index	
EINECS, ELINCS, NLP, REACH-IT List-No.	921-728-3
CAS	
content %	1-<5
Classification according to Regulation (EC) 1272/2008 (CLP), M-	Flam. Liq. 2, H225
factors	Skin Irrit. 2, H315
	STOT SE 3, H336
	Asp. Tox. 1, H304
	Aquatic Chronic 2, H411

Impurities, test data and additional information may have been taken into account in classifying and labelling the product.

For the text of the H-phrases and classification codes (GHS/CLP), see Section 16.

The substances named in this section are given with their actual, appropriate classification!

For substances that are listed in appendix VI, table 3.1 of the regulation (EC) no. 1272/2008 (CLP regulation) this means that all notes that may be given here for the named classification have been taken into account.

If, for example, the note P is applied for a hydrocarbon then this has already been taken into account for the classification named here.

Quote: "Note P - The classification as a carcinogen or mutagen need not apply if it can be shown that the substance contains less than 0,1 % w/w benzene (EINECS No 200-753-7)."

Article 4 of the regulation (EC) no. 1272/2008 (CLP regulation) was also observed and taken into account for the classification named here.

#### **SECTION 4: First aid measures**

#### 4.1 Description of first aid measures

First-aiders should ensure they are protected!

Never pour anything into the mouth of an unconscious person!

#### Inhalation

Remove person from danger area.

Supply person with fresh air and consult doctor according to symptoms.

If the person is unconscious, place in a stable side position and consult a doctor.

#### Skin contact

Remove polluted, soaked clothing immediately, wash thoroughly with plenty of water and soap, in case of irritation of the skin (flare), consult a doctor.

#### Eye contact

Remove contact lenses.

Wash thoroughly for several minutes using copious water. Seek medical help if necessary.

#### Ingestion

Typically no exposure pathway.

Rinse the mouth thoroughly with water.

Do not induce vomiting - give copious water to drink. Consult doctor immediately.

Danger of aspiration.

In case of vomiting, keep head low so that the stomach content does not reach the lungs.

#### 4.2 Most important symptoms and effects, both acute and delayed



Page 4 of 19

Safety data sheet according to Regulation (EC) No 1907/2006, Annex II

Revision date / version: 26.09.2022 / 0016

Replacing version dated / version: 01.11.2021 / 0015

Valid from: 26.09.2022 PDF print date: 30.03.2023

WD-40® Specialist® High Performance PTFE Lubricant

WD-40® SPECIALIST® PTFE

Irritation of the eyes

Irritation of the respiratory tract

Coughing Headaches Dizziness

Effects/damages the central nervous system

Unconsciousness

With long-term contact:

Drying of the skin.

Dermatitis (skin inflammation)

Ingestion: Nausea Vomiting

Danger of aspiration.

Oedema of the lungs

chemical pneumonitis (condition similar to pneumonia)

Other dangerous properties cannot be ruled out.

In certain cases, the symptoms of poisoning may only appear after an extended period / after several hours.

#### 4.3 Indication of any immediate medical attention and special treatment needed

Gastric lavage (stomach washing) only under endotracheal intubation.

Subsequent observation for pneumonia and pulmonary oedema.

Pulmonary oedema prophylaxis

# **SECTION 5: Firefighting measures**

# 5.1 Extinguishing media Suitable extinguishing media

CO<sub>2</sub>

Extinction powder Water jet spray

Alcohol resistant foam

# Unsuitable extinguishing media

High volume water jet

# 5.2 Special hazards arising from the substance or mixture

In case of fire the following can develop:

Oxides of carbon

Oxides of sulphur

Hydrofluoric acid

Toxic gases

Danger of bursting (explosion) when heated

Explosive vapour/air or gas/air mixtures.

# 5.3 Advice for firefighters

For personal protective equipment see Section 8.

In case of fire and/or explosion do not breathe fumes.

Protective respirator with independent air supply.

According to size of fire

Full protection, if necessary.

Cool container at risk with water.

Dispose of contaminated extinction water according to official regulations.

#### **SECTION 6: Accidental release measures**

# 6.1 Personal precautions, protective equipment and emergency procedures

# 6.1.1 For non-emergency personnel

In case of spillage or accidental release, wear personal protective equipment as specified in section 8 to prevent contamination.

Ensure sufficient ventilation, remove sources of ignition.

Avoid dust formation with solid or powder products.

Leave the danger zone if possible, use existing emergency plans if necessary.

Remove possible causes of ignition - do not smoke.

Ensure sufficient supply of air.

Avoid inhalation, and contact with eyes or skin.

If applicable, caution - risk of slipping.

#### 6.1.2 For emergency responders



Page 5 of 19

Safety data sheet according to Regulation (EC) No 1907/2006, Annex II

Revision date / version: 26.09.2022 / 0016

Replacing version dated / version: 01.11.2021 / 0015

Valid from: 26.09.2022 PDF print date: 30.03.2023

WD-40® Specialist® High Performance PTFE Lubricant

WD-40® SPECIALIST® PTFE

See section 8 for suitable protective equipment and material specifications.

#### 6.2 Environmental precautions

Prevent penetration into drains, cellars, working pits or other places in which accumulation could be hazardous.

Prevent surface and ground-water infiltration, as well as ground penetration.

If accidental entry into drainage system occurs, inform responsible authorities.

# 6.3 Methods and material for containment and cleaning up

If spray or gas escapes, ensure ample fresh air is available.

Without adequate ventilation, formation of explosive mixtures may be possible.

Active substance:

Soak up with absorbent material (e.g. universal binding agent, sand, diatomaceous earth) and dispose of according to Section 13.

#### 6.4 Reference to other sections

For personal protective equipment see Section 8 and for disposal instructions see Section 13.

# **SECTION 7: Handling and storage**

In addition to information given in this section, relevant information can also be found in section 8 and 6.1.

## 7.1 Precautions for safe handling

#### 7.1.1 General recommendations

Ensure good ventilation.

Avoid inhalation of the vapours.

Avoid contact with eyes or skin.

Keep away from sources of ignition - Do not smoke.

Take measures against electrostatic charging, if appropriate.

Do not use on hot surfaces.

Eating, drinking, smoking, as well as food-storage, is prohibited in work-room.

Observe directions on label and instructions for use.

Use working methods according to operating instructions.

#### 7.1.2 Notes on general hygiene measures at the workplace

General hygiene measures for the handling of chemicals are applicable.

Wash hands before breaks and at end of work.

Keep away from food, drink and animal feedingstuffs.

Remove contaminated clothing and protective equipment before entering areas in which food is consumed.

#### 7.2 Conditions for safe storage, including any incompatibilities

Keep out of access to unauthorised individuals.

Not to be stored in gangways or stair wells.

Store product closed and only in original packing.

Do not store with flammable or self-igniting materials.

Observe special regulations for aerosols!

Observe special storage conditions.

Observe special storage conditions.

Keep protected from direct sunlight and temperatures over 50°C.

Store in a well ventilated place.

Store cool.

#### 7.3 Specific end use(s)

No information available at present.

Observe the instructions for good working practice and the recommendations for risk assessment.

Consult hazardous substance information systems, e.g. from the professional associations, the chemical industry or different industries.

depending on the application (building materials, wood, chemistry, laboratory, leather, metal).

#### SECTION 8: Exposure controls/personal protection

# 8.1 Control parameters

Workplace exposure limit (WEL) of the total hydrocarbon solvent content of the mixture (RCP method according to EH40): 800 mg/m3

© Chemical Name	Hydrocarbons, C7, n-alkanes, isoalkanes, cyclics						
WEL-TWA: 800 mg/m3	WEL-STEL:						
Monitoring procedures:	<ul> <li>Draeger - Hydrocarbons 0,1%/c (81 03 571)</li> </ul>						
	<ul> <li>Draeger - Hydrocarbons 2/a (81 03 581)</li> </ul>						
	- Compur - KITA-187 S (551 174)						

® ® Page 6 of 19 Safety data sheet according to Regulation (EC) No 1907/2006, Annex II Revision date / version: 26.09.2022 / 0016 Replacing version dated / version: 01.11.2021 / 0015 Valid from: 26.09.2022 PDF print date: 30.03.2023 WD-40® Specialist® High Performance PTFE Lubricant WD-40® SPECIALIST® PTFE BMGV: ---Other information: (OEL acc. to RCPmethod, paragraphs 84-87, EH40) © Chemical Name Hydrocarbons, C7, n-alkanes, isoalkanes, cyclics OELV-8h: 100 ppm (573 mg/m3) ("Stoddard OELV-15min: solvent", [White spirit]) Draeger - Hydrocarbons 0,1%/c (81 03 571) Monitoring procedures: Draeger - Hydrocarbons 2/a (81 03 581) Compur - KITA-187 S (551 174) BLV: ---Other information: Chemical Name Hydrocarbons, C9-C11, n-alkanes, isoalkanes, cyclics, <2% aromatics WEL-TWA: 800 mg/m3 WEL-STEL: ---Draeger - Hydrocarbons 0,1%/c (81 03 571) Monitoring procedures: Draeger - Hydrocarbons 2/a (81 03 581) Compur - KITA-187 S (551 174) BMGV: ---Other information: (OEL acc. to RCPmethod, paragraphs 84-87, EH40) Chemical Name
Hydrocarbons, C9-C11, n-alkanes, isoalkanes, cyclics, <2% aromatics</p> OELV-8h: 100 ppm (573 mg/m3) ("Stoddard OELV-15min: solvent", [White spirit]) Draeger - Hydrocarbons 0,1%/c (81 03 571) Monitoring procedures: Draeger - Hydrocarbons 2/a (81 03 581) Compur - KITA-187 S (551 174) BLV: ---Other information: Chemical Name Hydrocarbons, C7-C9, isoalkanes WEL-TWA: 1200 mg/m3 WEL-STEL: ---Draeger - Hydrocarbons 0,1%/c (81 03 571) Monitoring procedures: Draeger - Hydrocarbons 2/a (81 03 581) Compur - KITA-187 S (551 174) Other information: (OEL acc. to RCP-BMGV: --method, paragraphs 84-87, EH40) Chemical Name Hydrocarbons, C7-C9, isoalkanes OELV-8h: 100 ppm (573 mg/m3) ("Stoddard OELV-15min: --solvent", [White spirit]) Monitoring procedures: Draeger - Hydrocarbons 0,1%/c (81 03 571) Draeger - Hydrocarbons 2/a (81 03 581) Compur - KITA-187 S (551 174) BLV: ---Other information: --- Chemical Name Petroleum gases, liquefied WEL-TWA: 1000 ppm (1750 mg/m3) (Liquefied WEL-STEL: 1250 ppm (2180 mg/m3) (Liquefied petroleum gas (LPG)) petroleum gas (LPG)) Monitoring procedures: BMGV: Other information: ---Chemical Name Petroleum gases, liquefied OELV-15min: 1000 ppm (Butane) OELV-8h: ------Monitoring procedures: Other information: BLV: Oil mist, mineral © Chemical Name WEL-TWA: 5 mg/m3 (Mineral oil, excluding WEL-STEL: --metal working fluids, ACGIH) Draeger - Oil Mist 1/a (67 33 031) Monitoring procedures: BMGV: Other information: Chemical Name Oil mist, mineral OELV-8h: 5 mg/m3 (Mineral oil, pure, highly & OELV-15min: --severely refined (inhalable)) Monitoring procedures: Draeger - Oil Mist 1/a (67 33 031) BLV: ---Other information: Hydrocarbons, C7, n-alkanes, isoalkanes, cyclics



Page 7 of 19

Safety data sheet according to Regulation (EC) No 1907/2006, Annex II

Revision date / version: 26.09.2022 / 0016

Replacing version dated / version: 01.11.2021 / 0015

Valid from: 26.09.2022 PDF print date: 30.03.2023

WD-40® Specialist® High Performance PTFE Lubricant

WD-40® SPECIALIST® PTFE

Area of application	pplication Exposure route / Environmental compartment		Descripto r	Value	Unit	Note
Consumer	Human - dermal	Long term, systemic effects	DNEL	149	mg/kg bw/d	
Consumer	Human - inhalation	Long term, systemic effects	DNEL	447	mg/m3	
Consumer	Human - oral	Long term, systemic effects	DNEL	149	mg/kg bw/d	
Workers / employees	Human - dermal	Long term, systemic effects	DNEL	300	mg/kg bw/d	
Workers / employees	Human - inhalation	Long term, systemic effects	DNEL	2085	mg/m3	

Hydrocarbons, C9-C11, n-alkanes, isoalkanes, cyclics, <2% aromatics								
Area of application	ea of application Exposure route / Environmental compartment		Descripto r	Value	Unit	Note		
Consumer	Human - dermal	Long term, systemic effects	DNEL	46	mg/kg bw/day			
Consumer	Human - inhalation	Long term, systemic effects	DNEL	185	mg/m3			
Consumer	Human - oral	Long term, systemic effects	DNEL	46	mg/kg bw/day			
Workers / employees	Human - dermal	Long term, systemic effects	DNEL	77	mg/kg bw/day			
Workers / employees	Human - inhalation	Long term, systemic effects	DNEL	871	mg/m3			

Hydrocarbons, C7-C9, isoalkanes								
Area of application	Exposure route / Environmental compartment	Effect on health	Descripto r	Value	Unit	Note		
Consumer	Human - oral	Long term, systemic effects	DNEL	699	mg/kg bw/day			
Consumer	Human - dermal	Long term, systemic effects	DNEL	699	mg/kg bw/day			
Consumer	Human - inhalation	Long term, systemic effects	DNEL	608	mg/m3			
Workers / employees	Human - dermal	Long term, systemic effects	DNEL	773	mg/kg bw/day			
Workers / employees	Human - inhalation	Long term, systemic effects	DNEL	2035	mg/m3			

- WEL-TWA = Workplace Exposure Limit Long-term exposure limit (8-hour TWA (= time weighted average) reference period) EH40. AGW = "Arbeitsplatzgrenzwert" (workplace limit value, Germany).
- (8) = Inhalable fraction (Directive 2017/164/EU, Directive 2004/37/CE). (9) = Respirable fraction (Directive 2017/164/EU, Directive 2004/37/CE). (11) = Inhalable fraction (Directive 2004/37/CE). (12) = Inhalable fraction. Respirable fraction in those Member States that implement, on the date of the entry into force of this Directive, a biomonitoring system with a biological limit value not exceeding 0,002 mg Cd/g creatinine in urine (Directive 2004/37/CE). | WEL-STEL = Workplace Exposure Limit Short-term exposure limit (15-minute reference period).
- (8) = Inhalable fraction (2017/164/EU, 2017/2398/EU). (9) = Respirable fraction (2017/164/EU, 2017/2398/EU). (10) = Short-term exposure limit value in relation to a reference period of 1 minute (2017/164/EU). | BMGV = Biological monitoring guidance value EH40. BGW = "Biologischer Grenzwert" (biological limit value, Germany) | Other information: Sen = Capable of causing occupational asthma. Sk = Can be absorbed through skin. Carc = Capable of causing cancer and/or heritable genetic damage.
- \*\* = The exposure limit for this substance is repealed through the TRGS 900 (Germany) of January 2006 with the goal of revision. (13) = The substance can cause sensitisation of the skin and of the respiratory tract (Directive 2004/37/CE), (14) = The substance can cause sensitisation of the skin (Directive 2004/37/CE).
- © OELV-8h = Occupational Exposure Limit Value (8-hour reference period). (IFV) = Inhalable Fraction and Vapour. (I) = Inhalable Fraction. (R) = Respirable Fraction.
- (8) = Inhalable fraction (Directive 2017/164/EU, Directive 2004/37/CE). (9) = Respirable fraction (Directive 2017/164/EU, Directive 2004/37/CE). (11) = Inhalable fraction (Directive 2004/37/CE). (12) = Inhalable fraction. Respirable fraction in those Member States that implement, on the date of the entry into force of this Directive, a biomonitoring system with a biological limit value not exceeding

(B) (RL

Page 8 of 19

Safety data sheet according to Regulation (EC) No 1907/2006, Annex II

Revision date / version: 26.09.2022 / 0016

Replacing version dated / version: 01.11.2021 / 0015

Valid from: 26.09.2022 PDF print date: 30.03.2023

WD-40® Specialist® High Performance PTFE Lubricant

WD-40® SPECIALIST® PTFE

0,002 mg Cd/g creatinine in urine (Directive 2004/37/CE). |

OELV-15min = Occupational Exposure Limit Value (15-minute reference period). (IFV) = Inhalable Fraction and Vapour. (I) = Inhalable Fraction. (R) = Respirable Fraction.

(8) = Inhalable fraction (2017/164/EU, 2017/2398/EU). (9) = Respirable fraction (2017/164/EU, 2017/2398/EU). (10) = Short-term exposure limit value in relation to a reference period of 1 minute (2017/164/EU).

BLV = Biological limit value |

Other information: Carc1A, Carc1B = carcinogenic substance, Cat. 1A or 1B. Muta1A, Muta1B = mutagenic substance, Cat. 1A or 1B. Repr1A, Repr1B = Substances known to be toxic for reproduction, Cat. 1A or 1B. Sk = can be absorbed through skin. Asphx = asphyxiant. Sen = Respiratory sensitizer. BOELV = Binding Occupational Exposure Limit Values. IOELV = Indicative Occupational Exposure Limit Values.

(13) = The substance can cause sensitisation of the skin and of the respiratory tract (Directive 2004/37/CE), (14) = The substance can cause sensitisation of the skin (Directive 2004/37/CE).

#### 8.2 Exposure controls

# 8.2.1 Appropriate engineering controls

Ensure good ventilation. This can be achieved by local suction or general air extraction.

If this is insufficient to maintain the concentration under the WEL or AGW values, suitable breathing protection should be worn. Applies only if maximum permissible exposure values are listed here.

Suitable assessment methods for reviewing the effectiveness of protection measures adopted include metrological and non-metrological investigative techniques.

These are specified by e.g. EN 14042.

EN 14042 "Workplace atmospheres. Guide for the application and use of procedures for the assessment of exposure to chemical and biological agents".

### 8.2.2 Individual protection measures, such as personal protective equipment

General hygiene measures for the handling of chemicals are applicable.

Wash hands before breaks and at end of work.

Keep away from food, drink and animal feedingstuffs.

Remove contaminated clothing and protective equipment before entering areas in which food is consumed.

Eye/face protection:

With danger of contact with eyes.

Tight fitting protective goggles with side protection (EN 166).

Skin protection - Hand protection:

Normally not necessary.

with long-term contact:

If applicable

Protective nitrile gloves (EN ISO 374).

Minimum layer thickness in mm:

0,4

Permeation time (penetration time) in minutes:

>= 480

Protective Viton® / fluoroelastomer gloves (EN ISO 374).

Minimum layer thickness in mm:

0,4

Permeation time (penetration time) in minutes:

>= 480

Protective hand cream recommended.

Skin protection - Other:

Protective working garments (e.g. safety shoes EN ISO 20345, long-sleeved protective working garments).

Respiratory protection:

Normally not necessary.

If OES or MEL is exceeded.

Filter A2 P2 (EN 14387), code colour brown, white

At high concentrations:

Respiratory protection appliance (insulation device) (e.g. EN 137 or EN 138)

Observe wearing time limitations for respiratory protection equipment.

Thermal hazards:

Not applicable

Additional information on hand protection - No tests have been performed.

(GB) (IRI

Page 9 of 19

Safety data sheet according to Regulation (EC) No 1907/2006, Annex II

Revision date / version: 26.09.2022 / 0016

Replacing version dated / version: 01.11.2021 / 0015

Valid from: 26.09.2022 PDF print date: 30.03.2023

WD-40® Specialist® High Performance PTFE Lubricant

WD-40® SPECIALIST® PTFE

In the case of mixtures, the selection has been made according to the knowledge available and the information about the contents. Selection of materials derived from glove manufacturer's indications.

Final selection of glove material must be made taking the breakthrough times, permeation rates and degradation into account. Selection of a suitable glove depends not only on the material but also on other quality characteristics and varies from manufacturer to manufacturer.

In the case of mixtures, the resistance of glove materials cannot be predicted and must therefore be tested before use.

The exact breakthrough time of the glove material can be requested from the protective glove manufacturer and must be observed.

### 8.2.3 Environmental exposure controls

No information available at present.

# **SECTION 9: Physical and chemical properties**

# 9.1 Information on basic physical and chemical properties

Physical state: Aerosol. Active substance: liquid.

Colour: Light brown Odour: Hydrocarbons

Melting point/freezing point:

There is no information available on this parameter.

Boiling point or initial boiling point and boiling range: n.a

Flammability: Does not apply to aerosols.

Lower explosion limit: 0,8 Vol-% Upper explosion limit: 9 Vol-%

Flash point:

Auto-ignition temperature:

Does not apply to aerosols.

Does not apply to aerosols.

Decomposition temperature: There is no information available on this parameter.

pH: Mixture is non-soluble (in water). Kinematic viscosity: Does not apply to aerosols.

Solubility: Insoluble

Partition coefficient n-octanol/water (log value): Does not apply to mixtures.

Vapour pressure: There is no information available on this parameter.

Density and/or relative density: 0,706 g/ml

Relative vapour density:

Does not apply to aerosols.

Particle characteristics:

Does not apply to aerosols.

9.2 Other information

Explosives: Product is not explosive. Possible build up of explosive/highly

flammable vapour/air mixture.

Oxidising liquids: No Bulk density: n.a.

# **SECTION 10: Stability and reactivity**

## 10.1 Reactivity

The product has not been tested.

#### 10.2 Chemical stability

Stable with proper storage and handling.

#### 10.3 Possibility of hazardous reactions

No decomposition if used as intended.

#### 10.4 Conditions to avoid

Heating, open flame, ignition sources

Pressure increase will result in danger of bursting.

# 10.5 Incompatible materials

Avoid contact with strong oxidizing agents.

# 10.6 Hazardous decomposition products

No decomposition when used as directed.

# **SECTION 11: Toxicological information**

# 11.1. Information on hazard classes as defined in Regulation (EC) No 1272/2008

Possibly more information on health effects, see Section 2.1 (classification).

WD-40® Specialist® High Performance PTFE Lubricant

WD-40® SPECIALIST® PTFE

Toxicity / effect	Endpoint	Value	Unit	Organism	Test method	Notes



Page 10 of 19
Safety data sheet according to Regulation (EC) No 1907/2006, Annex II
Revision date / version: 26.09.2022 / 0016
Replacing version dated / version: 01.11.2021 / 0015
Valid from: 26.09.2022

PDF print date: 30.03.2023

Acute toxicity, by oral route:	n.d.a.
Acute toxicity, by dermal	n.d.a.
route:	
Acute toxicity, by inhalation:	n.d.a.
Skin corrosion/irritation:	n.d.a.
Serious eye	n.d.a.
damage/irritation:	
Respiratory or skin	n.d.a.
sensitisation:	
Germ cell mutagenicity:	n.d.a.
Carcinogenicity:	n.d.a.
Reproductive toxicity:	n.d.a.
Specific target organ toxicity -	n.d.a.
single exposure (STOT-SE):	
Specific target organ toxicity -	n.d.a.
repeated exposure (STOT-	
RĖ):	
Aspiration hazard:	n.d.a.
Symptoms:	n.d.a.

Toxicity / effect	Endpoint	Value	Unit	Organism	Test method	Notes
Acute toxicity, by oral route:	LD50	>5840	mg/kg	Rat	OECD 401 (Acute	Analogous
• • •					Oral Toxicity)	conclusion
Acute toxicity, by dermal	LD50	>2920	mg/kg	Rat	OECD 402 (Acute	Analogous
route:					Dermal Toxicity)	conclusion
Acute toxicity, by inhalation:	LC50	>23,3	mg/l/4h	Rat	OECD 403 (Acute	Analogous
					Inhalation Toxicity)	conclusion
Skin corrosion/irritation:				Rabbit	OECD 404 (Acute	Irritant
					Dermal	
					Irritation/Corrosion)	
Serious eye				Rabbit		Not irritant
damage/irritation:					0505 400 (01)	N. / I.
Respiratory or skin				Guinea pig	OECD 406 (Skin	No (skin
sensitisation:					Sensitisation)	contact)
Germ cell mutagenicity:					OECD 476 (In Vitro	Negative
					Mammalian Cell Gene	
Carcinogenicity:					Mutation Test)	Negative
Reproductive toxicity:	NOAEL	9000	ppm	Rat	OECD 416 (Two-	Negative
Reproductive toxicity.	NOALL	9000	ppiii	Nai	generation	ivegative
					Reproduction Toxicity	
					Study)	
Aspiration hazard:					Otddy)	Yes
Symptoms:						diarrhoea,
Cymptome.						headaches,
						dizziness.
						nausea and
						vomiting.
Symptoms:						drowsiness,
						unconsciousne
						S,
						heart/circulator
						disorders,
						headaches,
						cramps,
						drowsiness,
						mucous
						membrane
						irritation,
						dizziness,
						nausea and
						vomiting.,
						diarrhoea



Page 11 of 19 Safety data sheet according to Regulation (EC) No 1907/2006, Annex II

Revision date / version: 26.09.2022 / 0016 Replacing version dated / version: 01.11.2021 / 0015 Valid from: 26.09.2022

PDF print date: 30.03.2023

Toxicity / effect	Endpoint	Value	Unit	Organism	Test method	Notes
Acute toxicity, by oral route:	LD50	>5000	mg/kg	Rat	OECD 401 (Acute Oral Toxicity)	
Acute toxicity, by dermal route:	LD50	>5000	mg/kg	Rabbit	OECD 402 (Acute Dermal Toxicity)	
Acute toxicity, by inhalation:	LD50	>18,5	mg/l/4h	Rat	OECD 403 (Acute Inhalation Toxicity)	
Skin corrosion/irritation:				Rabbit	OECD 404 (Acute Dermal Irritation/Corrosion)	Not irritant, Repeated exposure may cause skin dryness or cracking.
Skin corrosion/irritation:						Repeated exposure may cause skin dryness or cracking.
Serious eye damage/irritation:				Rabbit	OECD 405 (Acute Eye Irritation/Corrosion)	Not irritant
Respiratory or skin sensitisation:				Guinea pig	OECD 406 (Skin Sensitisation)	No (skin contact)
Germ cell mutagenicity:				Salmonella typhimurium	OECD 471 (Bacterial Reverse Mutation Test)	Negative, Analogous conclusion
Germ cell mutagenicity:				Human being	OECD 473 (In Vitro Mammalian Chromosome Aberration Test)	Negative, Analogous conclusion
Germ cell mutagenicity:				Mouse	OECD 476 (In Vitro Mammalian Cell Gene Mutation Test)	Negative, Analogous conclusion
Germ cell mutagenicity:				Rat	OECD 478 (Genetic Toxicology - Rodent dominant Lethal Test)	Negative, Analogous conclusion
Germ cell mutagenicity:					OECD 479 (Genetic Toxicology - In Vitro Sister Chromatid Exchange assay in Mammalian Cells)	Negative, Analogous conclusion Chinese hamster
Reproductive toxicity:					OECD 414 (Prenatal Developmental Toxicity Study)	Negative, Analogous conclusion
Carcinogenicity:	NOAEC	1100	mg/m3	Mouse	OECD 453 (Combined Chronic Toxicity/Carcinogenicit y Studies)	Female
Carcinogenicity:	NOAEC	>= 2200	mg/m3	Mouse	OECD 453 (Combined Chronic Toxicity/Carcinogenicit y Studies)	Male
Reproductive toxicity (Effects on fertility):	NOAEL	>= 3000	mg/kg bw/d	Rat	OECD 415 (One- Generation Reproduction Toxicity Study)	Male
Reproductive toxicity (Effects on fertility):	NOAEL	>= 1500	mg/kg bw/d	Rat	OECD 415 (One- Generation Reproduction Toxicity Study)	Female
Specific target organ toxicity - single exposure (STOT-SE):						May cause drowsiness or dizziness., STOT SE 3, H336
Aspiration hazard:						Yes



Page 12 of 19
Safety data sheet according to Regulation (EC) No 1907/2006, Annex II
Revision date / version: 26.09.2022 / 0016
Replacing version dated / version: 01.11.2021 / 0015
Valid from: 26.09.2022

PDF print date: 30.03.2023

Symptoms:						unconsciousnes s, headaches, dizziness, discoloration of the skin, vomiting, diarrhoea
Specific target organ toxicity - repeated exposure (STOT-RE), oral:	NOAEL	3000	mg/kg/d	Rat	OECD 408 (Repeated Dose 90-Day Oral Toxicity Study in Rodents)	Analogous conclusion
Specific target organ toxicity - repeated exposure (STOT-RE), inhalat.:	NOAEC	1444	ppm	Rat	OECD 413 (Subchronic Inhalation Toxicity - 90-Day Study)	Analogous conclusion

Hydrocarbons, C7-C9, isoalk Toxicity / effect	Endpoint	Value	Unit	Organism	Test method	Notes
Acute toxicity, by oral route:	LD50	>5000	mg/kg	Rat	OECD 401 (Acute	
			1119,119		Oral Toxicity)	
Acute toxicity, by dermal	LD50	>2000	mg/kg	Rabbit	OECD 402 (Acute	
route:		1 2000			Dermal Toxicity)	
Acute toxicity, by inhalation:	LC50	>9,4	mg/l	Rat	OECD 403 (Acute	Aerosol
		, , ,	1119,1		Inhalation Toxicity)	
Acute toxicity, by inhalation:	LC50	>20	mg/l/4h	Rat	OECD 403 (Acute	Vapours
ricate termony, by minanamenn			1.1.9, 1, 1.1		Inhalation Toxicity)	. apou.o
Skin corrosion/irritation:				Rabbit	OECD 404 (Acute	Irritant
					Dermal	
					Irritation/Corrosion)	
Serious eye				Rabbit	OECD 405 (Acute	Not irritant
damage/irritation:				Rabbit	Eye	110t iiiitaiit
damage/irritation.					Irritation/Corrosion)	
Respiratory or skin				Guinea pig	OECD 406 (Skin	Not sensitizisin
sensitisation:				Our lea pig	Sensitisation)	TVOC SCHSICIZISH
Germ cell mutagenicity:					OECD 471 (Bacterial	Negative
Germ cen matagementy.					Reverse Mutation	ivegative
					Test)	
Germ cell mutagenicity:				Rat	OECD 478 (Genetic	Negative
Germ cell mutagenicity.				Rai	Toxicology - Rodent	Negative
					dominant Lethal Test)	
Corm cell mutaganisitus					OECD 473 (In Vitro	Negative
Germ cell mutagenicity:						inegative
					Mammalian	
					Chromosome	
O					Aberration Test)	NI
Germ cell mutagenicity:					OECD 476 (In Vitro	Negative
					Mammalian Cell Gene	
<u> </u>					Mutation Test)	N1 0
Reproductive toxicity:					OECD 414 (Prenatal	Negative,
					Developmental	Analogous
					Toxicity Study)	conclusion
Reproductive toxicity:					OECD 416 (Two-	Negative,
					generation	Analogous
					Reproduction Toxicity	conclusion
					Study)	
Specific target organ toxicity -						May cause
single exposure (STOT-SE):						drowsiness or
						dizziness.,
						STOT SE 3,
						H336
Specific target organ toxicity -	NOAEC	1200	ppm	Rat	OECD 413	Negative,
repeated exposure (STOT-					(Subchronic Inhalation	Analogous
RÉ):					Toxicity - 90-Day	conclusion
					Study)	
Aspiration hazard:						Yes



Page 13 of 19

Safety data sheet according to Regulation (EC) No 1907/2006, Annex II

Revision date / version: 26.09.2022 / 0016

Replacing version dated / version: 01.11.2021 / 0015

Valid from: 26.09.2022 PDF print date: 30.03.2023

WD-40® Specialist® High Performance PTFE Lubricant

WD-40® SPECIALIST® PTFE

Symptoms:			headaches,
			mucous
			membrane
			irritation,
			dizziness

Petroleum gases, liquefied											
Toxicity / effect	Endpoint	Value	Unit	Organism	Test method	Notes					
Acute toxicity, by inhalation:	LC50	>5	mg/l								
Skin corrosion/irritation:						Not irritant					
Serious eye						Not irritant					
damage/irritation:											
Respiratory or skin						No (skin					
sensitisation:						contact)					
Aspiration hazard:						No					

# 11.2. Information on other hazards

WD-40® Specialist® High Performance PTFE Lubricant WD-40® SPECIALIST® PTFE											
Toxicity / effect	Endpoint	Value	Unit	Organism	Test method	Notes					
Endocrine disrupting						Does not apply					
properties:						to mixtures.					
Other information:						No other					
						relevant					
						information					
						available on					
						adverse effects					
						on health.					

# **SECTION 12: Ecological information**

Possibly more information on environmental effects, see Section 2.1 (classification).

WD-40® Specialist® H WD-40® SPECIALIST®		nce PTFE L	ubricant	,	,		
Toxicity / effect	Endpoint	Time	Value	Unit	Organism	Test method	Notes
12.1. Toxicity to fish:							n.d.a.
12.1. Toxicity to							n.d.a.
daphnia:							
12.1. Toxicity to algae:							n.d.a.
12.2. Persistence and							Isolate as
degradability:							much as
							possible with
							an oil separator.
12.3. Bioaccumulative							n.d.a.
potential:							
12.4. Mobility in soil:							n.d.a.
12.5. Results of PBT							n.d.a.
and vPvB assessment							
12.6. Endocrine							Does not apply
disrupting properties:							to mixtures.
12.7. Other adverse							No information
effects:							available on
							other adverse
							effects on the
							environment

Hydrocarbons, C7, n-alkanes, isoalkanes, cyclics											
Toxicity / effect	Endpoint	Time	Value	Unit	Organism	Test method	Notes				
12.1. Toxicity to fish:	LC50	96h	13,4	mg/l	Oncorhynchus mykiss						
12.1. Toxicity to fish:	LL50	96h	>13,4	mg/l	Oncorhynchus mykiss	OECD 203 (Fish, Acute Toxicity Test)					



Page 14 of 19
Safety data sheet according to Regulation (EC) No 1907/2006, Annex II
Revision date / version: 26.09.2022 / 0016
Replacing version dated / version: 01.11.2021 / 0015
Valid from: 26.09.2022

PDF print date: 30.03.2023

12.1. Toxicity to fish:	NOELR	28d	1,53	mg/l	Oncorhynchus mykiss	QSAR	
12.1. Toxicity to daphnia:	NOELR	21d	1	mg/l	Daphnia magna	OECD 211 (Daphnia magna Reproduction Test)	
12.1. Toxicity to algae:	EC50	72h	10 - 30	mg/l	Pseudokirchnerie Ila subcapitata		
12.1. Toxicity to algae:	NOELR	72h	10	mg/l	Pseudokirchnerie Ila subcapitata		
12.1. Toxicity to algae:	ErL50	72h	10-30	mg/l	Pseudokirchnerie Ila subcapitata	OECD 201 (Alga, Growth Inhibition Test)	
12.1. Toxicity to algae:	NOELR	72h	6,3	mg/l	Pseudokirchnerie Ila subcapitata	OECD 201 (Alga, Growth Inhibition Test)	
12.2. Persistence and degradability:		28d	98	%		OECD 301 F (Ready Biodegradability - Manometric Respirometry Test)	Readily biodegradable
Water solubility:			2,6	mg/l		,	25°C

Toxicity / effect	Endpoint	Time	Value	Unit	Organism	Test method	Notes
12.1. Toxicity to fish:	NOELR	28d	0,13	mg/l	Oncorhynchus	QSAR	
					mykiss		
12.1. Toxicity to fish:	LC50	96h	>1000	mg/l	Oncorhynchus	OECD 203	
					mykiss	(Fish, Acute	
						Toxicity Test)	
12.1. Toxicity to	EC50	48h	>1000	mg/l	Daphnia magna	OECD 202	
daphnia:						(Daphnia sp.	
						Acute	
						Immobilisation	
						Test)	
12.1. Toxicity to algae:	ErC50	72h	>1000	mg/l	Pseudokirchnerie	OECD 201	
					lla subcapitata	(Alga, Growth	
						Inhibition Test)	
12.1. Toxicity to algae:	EbC50	72h	>1000	mg/l	Pseudokirchnerie	OECD 201	
					lla subcapitata	(Alga, Growth	
						Inhibition Test)	
12.1. Toxicity to algae:	NOELR	72h	100	mg/l	Raphidocelis	OECD 201	
					subcapitata	(Alga, Growth	
						Inhibition Test)	
12.1. Toxicity to algae:	NOELR	72h	3	mg/l	Pseudokirchnerie	OECD 201	
					lla subcapitata	(Alga, Growth	
						Inhibition Test)	
12.2. Persistence and		28d	80	%		OECD 301 F	Readily
degradability:						(Ready	biodegradable
						Biodegradability -	
						Manometric	
						Respirometry	
						Test)	
12.3. Bioaccumulative			5-6,7			·	High
potential:							
12.5. Results of PBT							No PBT
and vPvB assessment							substance, No
							vPvB substanc
Toxicity to bacteria:	EL50	48h	0,95	mg/l			QSAR

Hydrocarbons, C7-C9, isoalkanes											
Toxicity / effect	Endpoint	Time	Value	Unit	Organism	Test method	Notes				
12.1. Toxicity to fish:	LC0		0,11	mg/l	Oncorhynchus mykiss	OECD 203 (Fish, Acute Toxicity Test)					

(B) (RL)

Page 15 of 19

Safety data sheet according to Regulation (EC) No 1907/2006, Annex II

Revision date / version: 26.09.2022 / 0016

Replacing version dated / version: 01.11.2021 / 0015

Valid from: 26.09.2022 PDF print date: 30.03.2023

WD-40® Specialist® High Performance PTFE Lubricant

WD-40® SPECIALIST® PTFE

12.1. Toxicity to	EL50	48h	2,4	mg/l	Daphnia magna		
daphnia:			'				
12.1. Toxicity to daphnia:	NOEC/NOEL	21d	0,17	mg/l	Daphnia magna		
12.1. Toxicity to algae:	EL50	72h	12	mg/l	Pseudokirchnerie Ila subcapitata	OECD 201 (Alga, Growth Inhibition Test)	
12.2. Persistence and degradability:		28d	22	%		OECD 301 F (Ready Biodegradability - Manometric Respirometry Test)	Not readily but inherent biodegradable.
12.2. Persistence and degradability:		28d	22	%			Hardly biodegradable
12.5. Results of PBT and vPvB assessment							No PBT substance, No vPvB substance

Petroleum gases, liquefied											
Toxicity / effect	Endpoint	Time	Value	Unit	Organism	Test method	Notes				
12.1. Toxicity to fish:	LC50	96h	147,54	mg/l		QSAR					
12.3. Bioaccumulative							Not to be				
potential:							expected				
12.5. Results of PBT							No PBT				
and vPvB assessment							substance, No				
							vPvB substance				

# **SECTION 13: Disposal considerations**

#### 13.1 Waste treatment methods

#### For the substance / mixture / residual amounts

EC disposal code no.:

The waste codes are recommendations based on the scheduled use of this product.

Owing to the user's specific conditions for use and disposal, other waste codes may be

allocated under certain circumstances. (2014/955/EU)

 ${\tt 07~06~04}$  other organic solvents, washing liquids and mother liquors

Recommendation:

Sewage disposal shall be discouraged.

Pay attention to local and national official regulations.

Take full aerosol cans to problem waste collection.

Take emptied aerosol cans to valuable material collection.

# For contaminated packing material

Pay attention to local and national official regulations.

Recommendation:

Do not perforate, cut up or weld uncleaned container.

Recycling

15 01 04 metallic packaging

# **SECTION 14: Transport information**

#### **General statements**

Transport by road/by rail (ADR/RID)

14.1. UN number or ID number: 1950

14.2. UN proper shipping name:

**UN 1950 AEROSOLS** 

14.3. Transport hazard class(es): 2.1

14.4. Packing group:

14.5. Environmental hazards: environmentally hazardous

Tunnel restriction code:

Classification code:

5F
LQ:
1 L
Transport category:
2



Page 16 of 19

Safety data sheet according to Regulation (EC) No 1907/2006, Annex II

Revision date / version: 26.09.2022 / 0016

Replacing version dated / version: 01.11.2021 / 0015

Valid from: 26.09.2022 PDF print date: 30.03.2023

WD-40® Specialist® High Performance PTFE Lubricant

WD-40® SPECIALIST® PTFE

Transport by sea (IMDG-code)

14.1. UN number or ID number: 1950

14.2. UN proper shipping name:

UN 1950 AEROSOLS (HYDROCARBONS, C7)

14.3. Transport hazard class(es):

14.4. Packing group:

14.5. Environmental hazards: environmentally hazardous

Marine Pollutant: Yes
EmS: F-D, S-U

Transport by air (IATA)

14.1. UN number or ID number: 1950

14.2. UN proper shipping name: UN 1950 Aerosols, flammable

14.3. Transport hazard class(es):

14.4. Packing group:

14.5. Environmental hazards:

Not applicable

14.6. Special precautions for user

Persons employed in transporting dangerous goods must be trained.

All persons involved in transporting must observe safety regulations.

Precautions must be taken to prevent damage.

14.7. Maritime transport in bulk according to IMO instruments

Freighted as packaged goods rather than in bulk, therefore not applicable.

Minimum amount regulations have not been taken into account.

Danger code and packing code on request.

Comply with special provisions.

# **SECTION 15: Regulatory information**

# 15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture

Observe restrictions:

Comply with national regulations/laws governing the protection of young people at work (national implementation of the Directive 94/33/EC)!

Comply with trade association/occupational health regulations.

Directive 2012/18/EU ("Seveso III"), Annex I, Part 1 - The following categories apply to this product (others may also need to be

considered according to storage, handling etc.):

contribution and according to eterage, managing eterj.			
Hazard categories	Notes to Annex I	Qualifying quantity (tonnes) of	Qualifying quantity (tonnes) of
		dangerous substances as	dangerous substances as
		referred to in Article 3(10) for	referred to in Article 3(10) for
		the application of - Lower-tier	the application of - Upper-tier
		requirements	requirements
E2		200	500
P3a	11.1	150 (netto)	500 (netto)

~ 82 %

The Notes to Annex 1 of Directive 2012/18/EU, in particular those named in the tables here and notes 1-6, must be taken into account when assigning categories and qualifying quantities.

Directive 2010/75/EU (VOC):

# **REGULATION (EC) No 648/2004**

n.a.

Observe incident regulations.

National requirements/regulations on safety and health protection must be applied when using work equipment.

#### 15.2 Chemical safety assessment

A chemical safety assessment is not provided for mixtures.

#### **SECTION 16: Other information**

EU F0058

Revised sections: 2





® (RL

Page 17 of 19

Safety data sheet according to Regulation (EC) No 1907/2006, Annex II

Revision date / version: 26.09.2022 / 0016

Replacing version dated / version: 01.11.2021 / 0015

Valid from: 26.09.2022 PDF print date: 30.03.2023

WD-40® Specialist® High Performance PTFE Lubricant

WD-40® SPECIALIST® PTFE

Employee training in handling dangerous goods is required.

These details refer to the product as it is delivered.

Employee instruction/training in handling hazardous materials is required.

# Classification and processes used to derive the classification of the mixture in accordance with the ordinance (EG) 1272/2008 (CLP):

Classification in accordance with regulation	Evaluation method used
(EC) No. 1272/2008 (CLP)	
Skin Irrit. 2, H315	Classification according to calculation procedure.
Asp. Tox. 1, H304	Classification according to calculation procedure.
STOT SE 3, H336	Classification according to calculation procedure.
Aquatic Chronic 2, H411	Classification according to calculation procedure.
Aerosol 1, H222	Classification according to calculation procedure.
Aerosol 1, H229	Classification based on the form or physical state.

The following phrases represent the posted Hazard Class and Risk Category Code (GHS/CLP) of the product and the constituents (specified in Section 2 and 3).

H225 Highly flammable liquid and vapour.

H226 Flammable liquid and vapour.

H304 May be fatal if swallowed and enters airways.

H315 Causes skin irritation.

H336 May cause drowsiness or dizziness.

H411 Toxic to aquatic life with long lasting effects.

EUH066 Repeated exposure may cause skin dryness or cracking.

Skin Irrit. — Skin irritation

Asp. Tox. — Aspiration hazard

STOT SE — Specific target organ toxicity - single exposure - narcotic effects

Aquatic Chronic — Hazardous to the aquatic environment - chronic

Aerosol — Aerosols

Flam. Liq. — Flammable liquid

#### Key literature references and sources for data:

Regulation (EC) No 1907/2006 (REACH) and Regulation (EC) No 1272/2008 (CLP) as amended.

Guidelines for the preparation of safety data sheets as amended (ECHA).

Guidelines on labelling and packaging according to the Regulation (EG) Nr. 1272/2008 (CLP) as amended (ECHA).

Safety data sheets for the constituent substances.

ECHA Homepage - Information about chemicals.

GESTIS Substance Database (Germany).

German Environment Agency "Rigoletto" information site on substances that are hazardous to water (Germany).

EU Occupation Exposure Limits Directives 91/322/EEC, 2000/39/EC, 2006/15/EC, 2009/161/EU, (EU) 2017/164, (EU) 2019/1831, each as amended.

National Lists of Occupational Exposure Limits for each country as amended.

Regulations on the transport of hazardous goods by road, rail, sea and air (ADR, RID, IMDG, IATA) as amended.

#### Any abbreviations and acronyms used in this document:

acc., acc. to according, according to

ADR Accord européen relatif au transport international des marchandises Dangereuses par Route (= European Agreement concerning the International Carriage of Dangerous Goods by Road)

AOX Adsorbable organic halogen compounds

approx. approximately Art., Art. no. Article number

ASTM ASTM International (American Society for Testing and Materials)

ATE Acute Toxicity Estimate

BAM Bundesanstalt für Materialforschung und -prüfung (Federal Institute for Materials Research and Testing, Germany)

BAuA Bundesanstalt für Arbeitsschutz und Arbeitsmedizin (= Federal Institute for Occupational Health and Safety, Germany)

BCF Bioconcentration factor

BSEF The International Bromine Council

bw body weight

-GB (RL) -

Page 18 of 19

Safety data sheet according to Regulation (EC) No 1907/2006, Annex II

Revision date / version: 26.09.2022 / 0016

Replacing version dated / version: 01.11.2021 / 0015

Valid from: 26.09.2022 PDF print date: 30.03.2023

WD-40® Specialist® High Performance PTFE Lubricant

WD-40® SPECIALIST® PTFE

CAS Chemical Abstracts Service

CLP Classification, Labelling and Packaging (REGULATION (EC) No 1272/2008 on classification, labelling and packaging of substances and mixtures)

CMR carcinogenic, mutagenic, reproductive toxic

DMEL Derived Minimum Effect Level
DNEL Derived No Effect Level
DOC Dissolved organic carbon

dw dry weight

e.g. for example (abbreviation of Latin 'exempli gratia'), for instance

EbCx, EyCx, EbLx (x = 10, 50) Effect Concentration/Level of x % on reduction of the biomass (algae, plants)

EC European Community
ECHA European Chemicals Agency

ECx, ELx (x = 0, 3, 5, 10, 20, 50, 80, 100) Effect Concentration/Level for x % effect

EEC European Economic Community

EINECS European Inventory of Existing Commercial Chemical Substances

ELINCS European List of Notified Chemical Substances

EN European Norms

EPA United States Environmental Protection Agency (United States of America)

ErCx, EµCx, ErLx (x = 10, 50) Effect Concentration/Level of x % on inhibition of the growth rate (algae, plants)

etc. et cetera EU European Union

EVAL Ethylene-vinyl alcohol copolymer

Fax. Fax number gen. general

GHS Globally Harmonized System of Classification and Labelling of Chemicals

GWP Global warming potential

Koc Adsorption coefficient of organic carbon in the soil

Kow octanol-water partition coefficient

IARC International Agency for Research on Cancer IATA International Air Transport Association IBC (Code) International Bulk Chemical (Code)

IMDG-code International Maritime Code for Dangerous Goods

incl. including, inclusive

**IUCLIDInternational Uniform Chemical Information Database** 

IUPAC International Union for Pure Applied Chemistry LC50 Lethal Concentration to 50 % of a test population

LD50 Lethal Dose to 50% of a test population (Median Lethal Dose)

Log Koc Logarithm of adsorption coefficient of organic carbon in the soil

Log Kow, Log Pow Logarithm of octanol-water partition coefficient

LQ Limited Quantities

MARPOL International Convention for the Prevention of Marine Pollution from Ships

n.a. not applicable n.av. not available n.c. not checked n.d.a. no data available

NIOSH National Institute for Occupational Safety and Health (USA)

NLP No-longer-Polymer

NOEC, NOEL No Observed Effect Concentration/Level

OECD Organisation for Economic Co-operation and Development

org. organic

OSHA Occupational Safety and Health Administration (USA)

PBT persistent, bioaccumulative and toxic

PE Polyethylene

PNEC Predicted No Effect Concentration

ppm parts per million PVC Polyvinylchloride

REACH Registration, Evaluation, Authorisation and Restriction of Chemicals (REGULATION (EC) No 1907/2006 concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals)

REACH-IT List-No. 9xx-xxx-x No. is automatically assigned, e.g. to pre-registrations without a CAS No. or other numerical identifier. List Numbers do not have any legal significance, rather they are purely technical identifiers for processing a submission via REACH-IT.

RID Règlement concernant le transport International ferroviaire de marchandises Dangereuses (= Regulation concerning the International Carriage of Dangerous Goods by Rail)

SVHC Substances of Very High Concern

Tel. Telephone

TOC Total organic carbon



Page 19 of 19

Safety data sheet according to Regulation (EC) No 1907/2006, Annex II

Revision date / version: 26.09.2022 / 0016

Replacing version dated / version: 01.11.2021 / 0015

Valid from: 26.09.2022 PDF print date: 30.03.2023

WD-40® Specialist® High Performance PTFE Lubricant

WD-40® SPECIALIST® PTFE

**UN RTDG** United Nations Recommendations on the Transport of Dangerous Goods

VOC Volatile organic compounds

vPvB very persistent and very bioaccumulative

wwt wet weight

The statements made here should describe the product with regard to the necessary safety precautions - they are not meant to guarantee definite characteristics - but they are based on our present up-to-date knowledge. No responsibility.

# These statements were made by: Chemical Check Platz 1-7, D-32839 Steinheim, Tel.: +49 5233 94 17 0, Fax: +49 5233 94 17 90

© by Chemical Check GmbH Gefahrstoffberatung. The copying or changing of this document is forbidden except with consent of the Chemical Check GmbH Gefahrstoffberatung.